

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT L/WB	90	95	90	95	90	95	90	95	90	95	100	95	100	95	97	100	102	95	97	100	102
						80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	85	85	85	85	87	87
MCW Series	Standard	MCW901116BRR1	1.5	18		73	55	66	51	59	46	51	41	41	67	52	63	49	54	66	43	52	45	57	37	46
MCW Series	Standard	MCW901116CRR1	2	20		81	61	73	56	65	51	57	46	41	74	58	70	49	60	73	48	59	50	63	41	51
MCW Series	Standard	MCW901116DOR1	3	23		93	71	84	65	75	59	66	52	46	85	67	80	63	69	84	56	67	57	73	47	58
MCW Series	Standard	MCW901117DDR1	3	26		102	80	93	73	84	67	74	60	95	76	90	72	78	94	64	76	65	82	55	67	
MCW Series	Standard	MCW901117FRR1	5	31		122	95	111	87	100	80	88	71	114	90	107	86	93	113	76	90	78	98	65	80	
MCW Series	Standard	MCW901126FRR1	5	45		181	138	164	127	147	115	128	102	167	131	157	124	135	165	109	130	112	142	92	114	
MCW Series	Standard	MCW901126HRR1	7.5	50		202	154	183	141	163	128	143	114	186	145	174	137	150	184	121	145	124	158	102	127	
MCW Series	Standard	MCW901127HRR1	7.5	57		225	174	205	161	184	146	162	131	209	166	197	158	171	207	139	166	143	180	119	147	
MCW Series	Standard	MCW901127JRR1	10	62		245	190	223	175	200	159	176	142	227	181	214	171	186	225	152	181	156	196	130	160	
MCW Series	Standard	MCW901136HRR1	7.5	66		266	203	241	186	215	169	188	150	245	192	230	181	198	242	159	191	164	209	136	168	
MCW Series	Standard	MCW901136JRR1	10	75		303	231	274	212	245	192	214	171	279	218	261	206	225	275	181	217	187	237	154	191	
MCW Series	Standard	MCW901137HRR1	7.5	75		296	229	270	212	242	193	213	172	275	219	259	207	225	273	183	218	189	237	157	193	
MCW Series	Standard	MCW901137JRR1	10	85		335	260	305	240	274	218	242	195	312	248	293	235	255	309	208	248	214	269	178	219	
MCW Series	Standard	MCW901137KRR1	15	93		367	285	334	262	300	239	264	214	341	271	321	257	279	338	227	271	234	294	195	240	
MCW Series	Standard	MCW901146KRR1	15	102		412	314	373	288	333	261	291	232	379	296	355	280	306	375	246	295	254	323	209	259	
MCW Series	Standard	MCW901147KRR1	15	117		461	358	420	330	378	301	333	269	429	341	404	324	351	425	286	341	294	370	245	302	
MCW Series	Standard	MCW901147LRR1	20	125		494	382	450	353	404	321	355	287	459	364	432	346	375	455	306	364	314	395	261	322	
MCW Series	Standard	MCW901156KRR1	15	134		541	412	490	378	437	342	382	305	498	389	467	368	402	492	324	388	334	424	275	341	
MCW Series	Standard	MCW901156LRR1	20	150		605	461	548	423	489	393	428	341	557	436	522	412	450	551	382	434	373	474	308	381	
MCW Series	Standard	MCW901157LRR1	20	170		670	520	611	480	549	437	483	391	623	496	587	470	510	618	416	495	428	537	356	438	
MCW Series	Standard	MCW901157NRR1	30	187		738	572	673	527	604	480	532	429	686	545	646	517	561	680	457	545	470	591	391	482	
MCW Series	Standard	MCW901546MRR1	25	214		856	657	778	605	696	549	611	489	790	622	742	589	642	781	519	620	535	676	441	546	
MCW Series	Standard	MCW901546NRR1	30	225		900	691	818	636	732	577	642	514	831	654	780	619	675	821	545	652	562	711	464	574	
MCW Series	Standard	MCW901547MRR1	25	239		930	731	852	676	769	617	681	554	868	698	820	663	717	861	589	697	605	754	506	619	
MCW Series	Standard	MCW901547NRR1	30	253		984	773	902	716	814	654	721	587	919	739	867	702	759	911	624	738	641	798	536	656	
MCW Series	Standard	MCW901548NRR1	30	270		1027	822	946	765	861	704	769	638	966	792	916	755	810	960	677	792	693	849	589	711	
MCW Series	Standard	MCW901548PRR1	40	298		1040 [1]	908	1040 [1]	845	950	777	849	704	1040 [1]	874	1011	834	894	1040 [1]	748	874	765	938	651	785	
MCW Series	Standard	MCW901549PRR1	40	309		1040 [1]	938	1040 [1]	877	978	811	880	740	1040 [1]	909	1040 [1]	870	927	1040 [1]	786	911	801	971	691	823	
MCW Series	Standard	MCW901556NRR1	30	286		1148	879	1042	807	932	732	816	652	1059	831	994	786	858	1047	692	828	713	904	589	729	
MCW Series	Standard	MCW901556PRR1	40	315		1265	968	1148	889	1026	806	899	718	1167	915	1095	866	945	1153	762	912	785	996	648	802	
MCW Series	Standard	MCW901556QRR1	50	336		1350	1033	1225	948	1095	860	958	765	1245	976	1168	923	1008	1231	812	973	838	1062	690	855	
MCW Series	Standard	MCW901557QRR1	50	379		1482	1159	1355	1071	1221	977	1079	876	1381	1106	1303	1050	1137	1370	932	1105	957	1196	800	980	
MCW Series	Standard	MCW901557RRR1	60	400		1565	1223	1430	1130	1289	1031	1139	925	1458	1167	1375	1109	1200	1446	983	1166	1010	1262	844	1035	
MCW Series	Standard	MCW901558RRR1	60	429		1580 [1]	1307	1508	1215	1369	1117	1222	1010	1541	1257	1459	1199	1287	1531	1074	1258	1099	1351	933	1127	
MCW Series	Standard	MCW901731KRR1	15	142		587	441	529	402	469	362	407	320	534	411	499	387	426	525	338	408	350	449	285	355	
MCW Series	Standard	MCW901732LRR1	20	179		715	552	651	508	584	461	513	411	659	520	619	492	537	651	434	517	449	554	371	456	
MCW Series	Standard	MCW901732MRR1	25	191		763	589	695	542	623	492	547	439	705	555	661	525	573	694	463	552	478	602	395	487	
MCW Series	Standard	MCW901736LRR1	20	178		717	547	650	502	580	455	508	405	661	517	619	489	534	653	430	515	444	563	366	453	
MCW Series	Standard	MCW901736MRR1	25	190		766	584	694	536	620	486	542	432	705	552	661	522	570	697	459	550	473	601	390	483	
MCW Series	Standard	MCW901737NRR1	30	218		858	667	783	615	703	560	620	502	798	636	752	603	654	791	534	635	549	689	458	562	
MCW Series	Standard	MCW901738NRR1	30	234		900	713	826	662	748	607	665	548	844	685	798	653	702	839	583	686	597	738	505	613	
MCW Series	Standard	MCW901746NRR1	30	261		1049	802	952	737	850	668	744	595	967	758	907	717	783	956	631	756	651	825	537	665	
MCW Series	Standard	MCW901747NRR1	30	285		1118	872	1021	805	919	734	811	657	1041	831	981	789	855	1033	699	831	719	900	600	736	
MCW Series	Standard	MCW901747PRR1	40	314		1232	960	1125	887	1012	808	894	724	1147	916	1081	870	942	1138	771	915	792	991	661	811	
MCW Series	Standard	MCW901748PRR1	40	337		1291	1027	1187	954	1076	859	979	819	1213	987	1148	941	1011	1205	841	988	861	1062	730	884	
MCW Series	Standard	MCW901748QRR1	50	357		1368	1088	1257	1010	1140	928	1016	838	1285	1046	1216	997	1071	1277	892	1047	913	1125	774	937	
MCW Series	Standard	MCW901756QRR1	50	381		1537	1171	1392	1075	1242	974	1086	867	1415	1107	1326	1046	1143	1399	920	1103	949	1205	782	969	
MCW Series	Standard	MCW901757QRR1	50	417		1642	1276	1497	1177	1346	1072	1186	960	1527	1216	1438	1154	1251	1514	1021	1215	1050	1317	876	1076	
MCW Series	Standard	MCW901757RRR1																								

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT/LWT	90	95	90	95	90	95	90	95	90	95	100	95	100	95	97	100	102	95	97	100	102	
						80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	85	85	85	85	85	85	85
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901127JRA1	10	62		245	190	223	175	200	159	176	142	227	181	214	171	186	225	152	181	156	196	130	160		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901136JRA1	7.5	96		203	203	241	186	215	169	188	150	242	193	230	181	198	243	159	181	164	209	136	168		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901137JRA1	10	75		303	231	274	212	245	192	214	171	279	218	261	206	225	275	181	217	187	237	154	191		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901137HRA1	7.5	75		296	229	270	212	242	193	213	172	275	219	259	207	225	273	183	218	189	237	157	193		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901137JRA1	10	85		335	260	305	240	274	218	242	195	312	248	293	235	255	309	208	248	214	269	178	219		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901137KRA1	15	93		367	285	334	262	300	239	264	214	341	271	321	257	279	338	227	271	234	294	195	240		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901146KRA1	15	102		412	314	373	288	333	261	291	232	379	296	355	280	306	375	246	295	254	323	209	259		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901147KRA1	15	117		461	358	420	330	378	301	333	269	429	341	404	324	351	425	286	341	294	370	245	302		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901147LRA1	20	125		494	382	450	353	404	321	355	287	459	364	432	346	375	455	306	364	314	395	261	322		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901156KRA1	15	134		541	412	490	378	437	342	382	305	498	389	467	368	402	492	324	388	334	424	275	341		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901156LRA1	20	150		605	461	548	423	489	383	428	341	557	436	522	412	450	551	362	434	374	474	308	381		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901157LRA1	20	170		670	520	611	480	549	437	483	391	623	496	587	470	510	618	416	495	428	537	356	438		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901157NRA1	30	187		738	572	673	527	604	480	532	429	686	545	646	517	561	680	457	545	470	591	391	482		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901546MRA1	25	214		856	657	778	605	696	549	611	489	790	622	742	589	642	781	519	620	535	676	441	546		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901546NRA1	30	225		900	691	818	636	732	577	642	514	831	654	780	619	675	821	545	652	567	711	464	574		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901547MRA1	25	239		930	731	852	676	769	617	681	554	868	698	820	663	717	861	589	697	605	754	506	619		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901547NRA1	30	253		984	773	902	716	814	654	721	587	919	739	867	702	759	911	624	738	641	798	536	656		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901548NRA1	30	270		1027	822	946	765	861	704	769	638	966	792	916	755	810	960	677	792	693	849	589	711		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901548PRA1	40	298		1040 [1]	908	1040 [1]	845	950	777	849	704	1040 [1]	874	1011	834	894	1040 [1]	748	874	765	938	651	785		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901549PRA1	40	309		1040 [1]	938	1040 [1]	877	978	811	880	740	1040 [1]	909	1040 [1]	870	927	1040 [1]	786	911	801	971	681	823		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901556NRA1	30	286		1148	879	1042	807	932	732	816	652	1059	831	994	786	858	1047	692	828	713	904	589	729		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901556PRA1	40	315		1265	968	1148	889	1026	806	899	718	1167	915	1095	866	945	1153	762	912	785	996	648	802		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901556QRA1	50	336		1350	1033	1225	948	1095	860	958	765	1245	976	1168	923	1008	1231	812	973	838	1062	690	855		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901557QRA1	50	379		1482	1159	1355	1071	1221	977	1079	876	1381	1106	1303	1050	1137	1370	932	1105	957	1196	800	980		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901557RRA1	60	400		1565	1223	1430	1130	1289	1031	1139	925	1458	1167	1375	1109	1200	1446	983	1166	1010	1262	844	1035		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901558RRA1	60	429		1580 [1]	1307	1508	1215	1369	1117	1222	1010	1541	1257	1459	1199	1287	1531	1074	1258	1099	1351	933	1127		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901731KRA1	15	142		587	441	529	402	469	362	407	320	534	411	499	387	426	525	338	408	350	449	285	355		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901732LRA1	20	179		715	552	651	508	584	461	513	411	659	520	619	492	537	651	434	517	449	564	371	456		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901732MRA1	25	191		763	589	695	542	623	492	547	439	703	555	661	525	573	694	463	552	478	602	395	487		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901736LRA1	20	178		717	547	650	502	580	455	508	405	661	517	619	489	534	653	430	515	444	563	366	453		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901736MRA1	25	190		766	584	694	536	620	486	542	432	705	552	661	522	570	697	459	550	473	601	390	483		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901737NRA1	30	218		858	667	783	615	703	560	620	502	798	636	752	603	654	791	534	635	549	689	538	652		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901738NRA1	30	234		900	713	826	662	748	607	665	548	844	685	798	653	702	839	583	686	597	738	505	613		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901746NRA1	30	261		1049	802	952	737	850	668	744	595	967	758	907	717	783	956	631	756	651	825	537	665		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901747NRA1	30	285		1118	872	1021	805	919	734	811	657	1041	831	981	789	855	1033	699	831	719	900	600	736		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901747PRA1	40	314		1232	960	1125	887	1032	809	884	724	1147	916	1081	870	942	1138	771	915	792	931	661	811		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901748PRA1	40	337		1291	1027	1187	954	1076	876	950	791	1213	987	1148	941	1011	1206	841	988	861	1062	730	884		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901748QRA1	50	357		1368	1088	1257	1010	1140	928	1016	838	1285	1046	1216	997	1071	1277	892	1047	913	1125	774	937		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901756QRA1	50	381		1537	1171	1392	1075	1242	974	1086	867	1415	1107	1326	1046	1143	1399	920	1103	949	1205	782	969		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901757QRA1	50	417		1642	1276	1497	1177	1346	1072	1186	960	1527	1216	1438	1154	1251	1514	1021	1215	1050	1317	876	1076		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901757RRA1	60	437		1721	1337	1569	1233	1410	1123	1243	1006	1601	1274	1507	1209	1311	1587	1070	1273	1100	1381	917	1127		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901758RRA1	60	469		1804	1429	1656	1326	1499	1216	1334	1097	1693	1373	1601	1308	1407	1682	1168	1375	1196	1479	1012	1228		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901946NRA1	30	251		1014	772	918	708	819	641	716	571	933	729	874	689	753	922	606	726	625	794	516	638		
MCW Series	2 ft (0.6 m) Outlet Attenuators	MCW901946PRA1	40	275		1112	846	1007	775	897	702	784	624	1023	799	959	755	825	1012	663	796	684					

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT LWT	90	95	90	95	90	95	90	95	95	100	95	100	95	97	100	102	95	97	100	102
						66	80	80	80	80	80	80	80	80	80	80	80	85	85	85	85	85	85	85	85
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901147LRC1	20	125		494	382	450	353	404	321	355	287	459	364	432	346	375	455	306	364	314	395	261	322
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901156RRC1	20	134		641	412	480	378	437	302	342	305	498	399	467	368	402	492	324	336	334	424	276	341
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901156LRC1	20	150		605	461	548	423	489	383	428	341	557	436	522	412	450	551	362	434	373	474	308	381
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901157LRC1	20	170		670	520	611	480	549	437	483	391	623	496	587	470	510	618	416	495	428	537	356	438
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901157NRC1	30	187		738	572	673	527	604	480	532	429	686	545	646	517	561	680	457	545	470	591	391	482
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901546MRC1	25	214		856	657	778	605	696	549	611	489	790	622	742	589	642	781	519	620	535	676	441	546
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901546NRC1	30	225		900	691	818	636	732	577	642	514	831	654	780	619	675	821	545	652	562	711	464	574
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901547MRC1	25	239		930	731	852	676	769	617	681	554	868	698	820	663	717	861	589	697	605	754	506	619
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901547NRC1	30	253		984	773	902	716	814	654	727	587	919	739	867	702	759	911	624	738	641	798	536	656
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901548NRC1	30	270		1027	822	946	765	861	704	769	638	966	792	916	755	810	960	677	792	693	849	589	711
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901548PRC1	40	298		1040 [1]	908	1040 [1]	845	950	777	849	704	1040 [1]	874	1011	834	894	1040 [1]	748	874	765	938	651	785
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901549PRC1	40	309		1040 [1]	938	1040 [1]	877	978	811	880	740	1040 [1]	909	1040 [1]	870	927	1040 [1]	786	911	801	971	691	823
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901556NRC1	30	286		1148	879	1042	807	932	732	816	652	1059	831	994	786	858	1047	692	828	713	904	589	729
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901556PRC1	40	315		1265	968	1148	889	1026	806	899	718	1167	915	1095	866	945	1153	762	912	785	996	648	802
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901556QRC1	50	336		1350	1033	1225	948	1095	860	958	765	1245	976	1168	923	1008	1231	812	973	838	1062	690	855
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901557QRC1	50	379		1482	1159	1355	1071	1221	977	1079	876	1381	1106	1303	1050	1137	1370	932	1105	957	1196	800	980
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901557RRC1	60	400		1565	1223	1430	1130	1289	1031	1139	925	1458	1167	1375	1109	1200	1446	983	1166	1010	1262	844	1035
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901558RRC1	60	429		1580 [1]	1307	1508	1215	1369	1117	1222	1010	1541	1257	1459	1199	1287	1531	1074	1258	1099	1351	933	1127
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901731KRC1	15	142		587	441	529	402	469	362	407	320	534	411	498	387	426	525	338	408	359	449	285	355
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901732LRC1	20	179		715	552	651	508	584	461	515	411	659	520	619	492	537	651	434	517	449	564	371	456
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901732MRC1	25	191		763	589	695	542	623	492	547	439	703	555	661	525	573	694	463	552	478	602	395	487
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901736LRC1	20	178		717	547	650	502	580	455	508	405	661	517	619	489	534	653	430	515	444	563	366	453
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901736MRC1	25	190		766	584	694	536	620	496	542	432	705	552	661	522	570	697	459	550	473	601	390	483
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901737NRC1	30	218		858	667	783	615	703	560	620	502	798	636	752	603	654	791	534	635	549	689	458	562
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901738NRC1	30	234		900	713	826	662	748	607	665	548	844	685	798	653	702	839	583	686	597	738	505	613
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901746NRC1	30	261		1049	802	952	737	850	668	744	595	967	758	907	717	783	956	631	756	651	825	537	665
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901747NRC1	30	285		1118	872	1021	805	919	734	811	657	1041	831	981	789	855	1033	699	831	719	900	600	736
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901747PRC1	40	314		1232	960	1125	887	1012	808	894	724	1147	916	1101	801	942	1138	771	915	792	991	661	811
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901748PRC1	40	337		1291	1027	1187	954	1076	875	959	791	1213	987	1148	941	1011	1205	841	988	861	1062	730	884
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901748QRC1	50	357		1368	1088	1257	1010	1140	928	1016	838	1285	1046	1216	997	1071	1277	892	1047	913	1125	774	937
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901756QRC1	50	381		1537	1171	1392	1075	1242	974	1086	867	1415	1107	1326	1046	1143	1399	920	1103	949	1205	782	969
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901757QRC1	50	417		1642	1276	1497	1177	1346	1072	1186	960	1527	1216	1438	1154	1251	1514	1021	1215	1050	1317	876	1076
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901757RRC1	60	437		1721	1337	1569	1233	1410	1123	1243	1006	1601	1274	1507	1209	1311	1587	1070	1273	1100	1381	917	1127
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901758RRC1	60	469		1804	1429	1656	1326	1499	1216	1334	1097	1693	1373	1601	1308	1407	1682	1168	1375	1196	1479	1012	1228
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901946NRC1	30	251		1104	772	918	708	819	641	716	571	933	729	874	689	753	922	606	726	625	794	516	638
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901946PRC1	40	275		1142	846	1007	775	897	702	784	624	1023	799	959	755	825	1012	683	796	684	870	563	699
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901947NRC1	30	280		1105	857	1007	790	904	719	796	644	1027	816	967	774	840	1019	685	816	704	885	687	821
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901947PRC1	40	309		1220	945	1111	872	998	793	879	710	1134	901	1067	854	927	1124	756	900	777	977	647	796
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901948NRC1	30	307		1185	936	1086	868	982	795	872	716	1111	899	1050	855	921	1104	763	900	781	968	660	803
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901948PRC1	40	340		1311	1036	1202	961	1088	881	966	794	1229	995	1162	948	1020	1221	846	966	866	1072	732	889
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901949PRC1	40	358		1359	1088	1251	1013	1137	933	1016	846	1282	1051	1215	1004	1074	1276	902	1054	920	1128	787	947
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901949QRC1	50	389		1475	1182	1358	1101	1235	1014	1105	920	1392	1143	1319	1091	1167	1385	981	1146	1001	1225	857	1030
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901949RRC1	60	416		1560 [1]	1264	1450	1178	1320	1086	1182	987	1485	1222	1409	1168	1248	1479	1051	1225	1072	1310	919	1103
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901956QRC1	50	375		1518	1153	1373	1058	1224	958	1069	852	1396	1089	1308	1029	1125	1380	905	1085	933	1186	770	953
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901956RRC1	60	401		1624	1233	1469	1131	1309	1024	1143	911	1494	1164	1399	1101	1203	1476	967	1160	997	1269	822	1018
MCW Series	4 ft (1.2 m) Outlet Attenuators	MCW901957QRC1	50</																						

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT LWT	90	95	90	95	90	95	90	95	90	95	100	95	100	95	97	100	102	95	97	100	102	
						80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	85	85	85	85	85	85	85
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901547NAR1	30	238		926	728	848	673	766	615	678	552	864	695	816	660	714	857	587	694	603	750	505	617		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901548PAR1	40	254		1466	774	980	720	810	663	724	600	909	745	852	711	762	935	637	652	739	554	669			
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901548PAR1	40	280.3		1040 [1]	854	983	795	894	731	799	662	1004	822	952	784	841	998	704	823	720	882	612	738		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901549PAR1	40	290.7		1040 [1]	883	1007	825	920	763	828	696	1031	855	980	818	872	1026	739	857	754	913	650	774		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901556NAR1	30	269		1080	827	981	760	876	689	767	613	996	782	935	740	807	985	651	779	671	850	554	685		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901556PAR1	40	296.3		1190	911	1080	836	965	758	845	675	1097	861	1030	815	889	1085	716	858	739	937	609	755		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901556QAR1	50	316.1		1270	971	1152	892	1030	809	902	720	1171	918	1099	869	948	1158	764	915	788	999	649	805		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901557QAR1	50	356.5		1394	1090	1275	1007	1149	910	1015	824	1300	1040	1225	988	1070	1289	877	1039	901	1125	752	922		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901557RAR1	60	376.3		1472	1151	1345	1063	1212	970	1072	870	1372	1098	1293	1043	1129	1360	925	1097	951	1187	794	973		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901558RAR1	60	403.6		1542	1229	1418	1143	1288	1050	1149	950	1449	1183	1373	1128	1211	1440	1010	1184	1033	1271	877	1060		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901731KAR1	15	133.6		552	415	498	379	442	341	383	301	502	387	469	364	401	494	318	383	329	422	268	334		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901732LAR1	20	168.4		673	519	613	478	549	434	482	387	620	489	583	463	505	612	409	487	422	531	349	429		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901732MAR1	25	179.7		718	554	654	510	586	463	515	413	661	522	622	494	539	653	436	519	450	566	372	458		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901736LAR1	20	167.5		675	515	612	473	546	428	477	381	621	486	583	460	502	614	405	485	417	529	344	426		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901736MAR1	25	178.7		721	549	653	504	583	457	510	407	664	519	622	491	536	656	432	517	445	565	367	455		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901737NAR1	30	205.1		807	627	736	579	662	527	583	472	751	598	707	567	615	745	502	597	516	648	431	529		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901738NAR1	30	220.1		846	671	777	623	704	571	623	515	794	645	751	614	660	789	549	645	562	694	475	577		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901746NAR1	30	245.5		987	755	895	693	800	628	700	560	910	713	854	675	737	900	594	711	612	776	505	625		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901747NAR1	30	268.1		1052	820	961	757	865	690	763	618	980	782	933	742	804	971	658	781	676	847	564	692		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901747PAR1	40	295.4		1159	903	1058	834	952	761	841	682	1079	862	1017	818	886	1070	725	861	745	933	622	763		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901748PAR1	40	317		1215	966	1116	897	1013	824	902	744	1141	929	1080	885	951	1134	792	930	810	999	687	832		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901748QAR1	50	335.8		1287	1023	1183	951	1073	873	956	788	1209	984	1144	938	1008	1201	839	985	858	1058	728	881		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901756QAR1	50	358.4		1446	1102	1310	1011	1169	916	1022	815	1331	1041	1248	984	1075	1316	865	1037	892	1133	736	911		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901757QAR1	50	392.3		1544	1200	1408	1107	1266	1008	1116	903	1437	1144	1353	1085	1177	1425	961	1143	988	1239	824	1012		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901757RAR1	60	411.1		1619	1258	1476	1160	1327	1057	1169	946	1506	1199	1418	1137	1233	1493	1007	1198	1035	1299	863	1060		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901758RAR1	60	441.2		1697	1345	1557	1248	1410	1154	1255	1032	1592	1292	1506	1231	1324	1582	1099	1293	1125	1391	952	1155		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901946NAR1	30	236.1		954	726	864	666	770	603	673	537	878	686	822	648	708	868	570	683	588	747	485	600		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901946PAR1	40	258.7		1046	795	947	729	844	660	737	587	963	751	902	710	776	952	624	749	643	818	530	657		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901947NAR1	30	263.4		1040	806	947	743	851	676	749	606	967	768	909	728	790	958	644	767	662	832	552	679		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901947PAR1	40	290.7		1148	889	1046	820	939	746	827	668	1067	848	1004	804	872	1058	711	847	731	919	609	749		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901948NAR1	30	288.8		1114	880	1022	816	924	748	821	674	1045	846	987	805	866	1038	718	846	735	911	621	755		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901948PAR1	40	319.8		1233	975	1131	904	1023	828	909	747	1156	936	1093	892	960	1149	796	937	815	1009	689	837		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901949PAR1	40	336.8		1279	1024	1177	953	1070	877	956	796	1206	989	1143	944	1010	1201	848	992	866	1061	741	891		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901949QAR1	50	365.9		1388	1112	1278	1036	1162	954	1039	866	1309	1075	1241	1026	1098	1303	923	1078	942	1153	806	968		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901949RAR1	60	391.3		1480	1189	1364	1108	1242	1022	1112	928	1397	1150	1326	1098	1174	1391	988	1153	1008	1232	865	1037		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901952QAR1	50	352.8		1428	1095	1292	995	1151	911	1005	802	1313	1025	1230	969	1058	1298	851	1021	878	1116	724	897		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901956PAR1	60	377.2		1528	1160	1382	1064	1231	963	1075	857	1405	1096	1315	1035	1132	1389	909	1091	930	1194	773	958		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901957QAR1	50	386.6		1531	1183	1393	1090	1250	992	1099	887	1422	1127	1337	1068	1160	1410	944	1126	971	1223	809	985		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901957RAR1	60	408.3		1617	1249	1472	1151	1320	1047	1160	936	1502	1190	1412	1128	1225	1489	997	1189	1025	1291	854	1050		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901958QAR1	50	435.6		1686	1328	1544	1230	1395	1126	1237	1014	1579	1275	1491	1213	1307	1569	1081	1276	1107	1375	935	1137		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901958RAR1	60	461.9		1787	1408	1637	1305	1479	1194	1312	1076	1674	1352	1581	1286	1386	1664	1147	1353	1174	1458	991	1206		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901959RAR1	60	482.6		1840	1467	1691	1364	1535	1254	1369	1136	1734	1417	1642	1352	1448	1726	1212	1421	1238	1522	1057	1274		
MCW Series	2 ft (0.6 m) Inlet Attenuators	MCW901959SAR1	80	533.4		2027	1621	1865	1509	1695	1389	1514	1259	1911	1566	1811	1495	1600	1903	1343	1571	1370	1681	1172	1411	</	

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT LWT	90	95	90	95	90	95	90	95	90	95	100	95	100	95	97	100	102	95	97	100	102
						80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	85	85	85	85	85	85
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901557RAA1	60	376.3		1472	1151	1345	1063	1212	970	1072	870	1372	1098	1293	1043	1129	1360	925	1097	951	1187	794	973	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901558RAA1	60	403.6		1542	1229	1418	1143	1288	1050	1139	950	1440	1183	1373	1128	1211	1440	1010	1184	1033	1271	877	1060	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901731KAA1	15	133.6		562	415	498	379	442	341	383	300	502	387	469	364	401	494	318	383	329	422	268	334	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901732LAA1	20	168.4		673	519	613	478	549	434	482	387	620	499	583	463	505	612	409	487	422	531	349	429	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901732MAA1	25	179.7		718	554	654	510	586	463	515	413	661	522	622	494	539	653	436	519	450	566	372	458	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901736LAA1	20	167.5		675	515	612	473	546	428	477	381	621	486	583	460	502	614	405	485	417	529	344	426	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901736MAA1	25	178.7		721	549	653	504	583	457	510	407	664	519	622	491	536	656	432	517	445	565	367	455	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901737NAA1	30	205.1		807	627	736	579	662	527	583	472	751	598	707	567	615	745	502	597	516	648	431	529	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901738NAA1	30	220.1		846	671	777	623	704	571	626	515	794	645	751	614	660	789	549	645	562	694	475	577	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901746NAA1	30	245.5		987	755	895	693	800	628	700	560	910	713	854	675	737	900	594	711	612	776	505	625	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901747NAA1	30	268.1		1052	820	961	757	865	690	763	618	980	782	923	742	804	971	658	781	676	847	564	692	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901747PAA1	40	295.4		1159	903	1058	834	952	761	841	682	1079	862	1017	818	886	1070	725	861	745	933	622	763	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901748PAA1	40	317		1215	966	1116	897	1013	824	904	744	1141	929	1080	885	951	1134	792	930	810	999	687	832	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901748QAA1	50	335.8		1287	1023	1183	951	1073	873	956	788	1209	984	1144	938	1008	1201	839	985	858	1058	728	881	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901756QAA1	50	358.4		1446	1102	1310	1011	1169	916	1022	815	1331	1041	1248	984	1075	1316	865	1037	892	1133	736	911	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901757QAA1	50	392.3		1544	1200	1408	1107	1266	1008	1116	903	1437	1144	1353	1085	1177	1425	961	1143	988	1239	824	1012	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901757RAA1	60	411.1		1619	1258	1476	1160	1327	1057	1169	946	1506	1199	1418	1137	1233	1493	1007	1198	1035	1299	863	1060	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901758RAA1	60	441.2		1697	1345	1557	1248	1410	1144	1255	1032	1592	1292	1506	1231	1324	1582	1099	1293	1125	1391	952	1155	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901948NAA1	30	236.1		954	726	864	666	770	603	673	537	878	686	822	648	708	868	570	683	588	747	485	600	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901946PAA1	40	258.7		1046	795	947	729	844	660	737	587	962	751	902	710	776	952	624	749	643	818	530	657	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901947NAA1	30	263.4		1040	806	947	743	851	676	749	606	967	768	909	728	790	958	644	767	662	832	552	679	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901947PAA1	40	290.7		1148	889	1046	820	939	746	827	668	1067	848	1004	804	872	1058	711	847	731	919	609	745	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901948NAA1	30	288.8		1114	880	1022	816	924	748	821	674	1045	846	987	805	866	1038	718	846	735	911	621	755	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901948PAA1	40	319.8		1233	975	1131	904	1023	828	909	747	1156	936	1093	892	960	1149	796	937	815	1009	689	837	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901949PAA1	40	336.8		1279	1024	1177	953	1070	877	956	796	1206	989	1143	944	1010	1201	848	992	866	1061	741	891	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901949QAA1	50	365.9		1388	1112	1278	1036	1162	954	1039	866	1309	1075	1241	1026	1098	1303	923	1078	942	1153	806	969	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901949RAA1	60	391.3		1480	1189	1364	1108	1242	1022	1112	928	1397	1150	1326	1098	1174	1391	988	1153	1008	1232	865	1037	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901956QAA1	50	352.8		1428	1085	1292	995	1151	901	1005	802	1313	1025	1230	968	1058	1298	851	1021	878	1116	724	897	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901956RAA1	60	377.2		1528	1160	1382	1064	1231	963	1075	857	1405	1095	1316	1035	1132	1389	909	1091	938	1194	773	958	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901957QAA1	50	386.6		1531	1183	1393	1090	1250	992	1099	887	1422	1127	1337	1068	1160	1410	944	1126	971	1223	809	995	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901957RAA1	60	408.3		1617	1249	1472	1151	1320	1047	1160	936	1502	1190	1412	1128	1225	1489	997	1189	1025	1291	854	1050	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901958QAA1	50	435.6		1686	1328	1544	1230	1395	1126	1237	1014	1579	1275	1491	1213	1307	1569	1081	1276	1107	1375	935	1137	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901958RAA1	60	461.9		1787	1408	1637	1305	1479	1194	1312	1076	1674	1352	1581	1286	1386	1664	1147	1353	1174	1458	991	1206	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901959RAA1	60	482.6		1840	1467	1691	1364	1535	1254	1369	1136	1734	1417	1642	1352	1448	1728	1212	1421	1238	1522	1057	1274	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901959QAA1	80	533.4		2027	1621	1865	1509	1695	1389	1514	1259	1911	1556	1811	1495	1600	1903	1343	1571	1370	1681	1172	1411	
MCW Series	2 ft (0.6 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901959RAA1	100	564.4		2148	1745	1976	1598	1794	1459	1602	1332	2025	1657	1918	1582	1693	2016	1420	1662	1449	1779	1240	1492	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901116BAC1	1.5	16.5		68	52	62	48	55	48	49	39	63	49	57	47	51	62	41	49	41	56	35	43	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901116CAC1	2	18.8		76	58	69	53	61	55	54	43	70	55	66	52	56	69	45	54	47	59	39	48	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901116DAC1	3	21.6		87	67	79	61	71	55	62	49	80	63	75	59	65	79	52	63	54	68	44	55	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901117DAC1	3	24.5		96	75	88	69	79	63	70	56	90	71	84	68	73	89	60	71	62	77	51	63	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901117FAC1	5	29.2		115	89	105	82	94	75	83	67	107	85	101	81	87	106	71	85	73	92	61	75	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901126FAC1	5	42.3		171	130	155	119	138	108	121	96	157	123	147	116	127	155	102	123	105	134	87	108	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901126HAC1	7.5	47		190	145	172	133	153	120	134	107	175	137	164	129	141	173	113	136	117	149	96	120	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901127HAC1	7.5	53.6		211	164	193	151	173	138	152	123	197	156	185	148	161	195	131	156	135	169	112	138	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901127JAC1	10	58.3		230	178	210	165	188	150	166	134	214	170	201	161	175	212	143	170	147	184	122	150	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901136HAC1	7.5	62.1		251	191	227	175	203	159	177	141	231	180	216	171	186	228	150	180	155	196	128	158	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901136JAC1	10																							

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown
 [2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT LWT	90	95	90	95	90	95	90	95	95	100	95	100	95	97	100	102	95	97	100	102	
						80	80	80	80	80	80	80	80	85	85	85	85	85	85	85	85	85	85	85	87	87
						66	66	68	68	70	70	72	72	75	75	76	76	78	78	78	78	80	80	80	80	80
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901738NAC1	30	220.1		846	671	777	623	704	571	626	515	794	645	751	614	660	769	549	645	562	694	475	577	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901746NAC1	30	245.5		937	756	895	693	803	628	703	560	910	713	834	675	737	900	594	711	612	776	506	636	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901747NAC1	30	268.1		1052	820	961	757	865	690	763	610	980	782	923	742	804	971	658	781	676	847	564	692	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901747PAC1	40	295.4		1159	903	1058	834	952	761	841	682	1079	862	1017	818	886	1070	725	861	745	933	622	763	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901748PAC1	40	317		1215	966	1116	897	1013	824	902	744	1141	929	1080	885	951	1134	792	930	810	999	687	832	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901748QAC1	50	335.8		1287	1023	1183	951	1073	873	956	788	1209	984	1144	938	1008	1201	839	985	858	1058	728	881	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901756QAC1	50	358.4		1446	1102	1310	1011	1169	916	1022	815	1331	1041	1248	984	1075	1316	865	1037	892	1133	736	911	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901757QAC1	50	392.3		1544	1200	1408	1107	1266	1008	1116	903	1437	1144	1353	1085	1177	1425	961	1143	988	1239	824	1012	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901757RAC1	60	411.1		1619	1258	1476	1160	1327	1057	1169	946	1506	1199	1418	1137	1233	1493	1007	1198	1035	1299	863	1060	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901758RAC1	60	441.2		1697	1345	1557	1248	1410	1144	1255	1032	1592	1292	1506	1231	1324	1582	1099	1293	1125	1391	952	1155	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901946NAC1	30	236.1		954	726	864	666	770	603	673	537	878	686	822	648	708	868	570	683	588	747	485	600	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901946PAC1	40	258.7		1046	795	947	729	844	660	737	587	963	751	902	710	776	952	624	749	643	818	530	657	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901947NAC1	30	263.4		1040	806	947	743	851	676	749	606	967	768	909	728	790	958	644	767	662	832	562	679	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901947PAC1	40	290.7		1148	889	1046	820	939	746	827	668	1067	848	1004	804	872	1058	711	847	731	919	609	749	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901948NAC1	30	288.8		1114	880	1022	816	924	748	821	674	1045	846	987	805	866	1038	718	846	735	911	621	755	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901948PAC1	40	319.8		1233	975	1131	904	1023	828	909	747	1156	936	1093	892	960	1149	796	937	815	1009	689	837	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901949PAC1	40	336.8		1279	1024	1177	953	1070	877	956	796	1206	989	1143	944	1010	1201	848	992	866	1061	741	891	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901949QAC1	50	365.9		1388	1112	1278	1036	1162	954	1039	866	1309	1075	1241	1026	1098	1303	923	1078	942	1153	806	969	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901949RAC1	60	391.3		1480	1189	1364	1108	1242	1022	1112	928	1397	1150	1326	1098	1174	1391	988	1153	1098	1232	895	1037	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901956QAC1	50	352.8		1428	1085	1292	995	1151	901	1005	802	1313	1025	1230	969	1058	1298	851	1021	878	1116	724	897	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901956RAC1	60	377.2		1528	1160	1382	1064	1231	963	1075	857	1405	1095	1316	1035	1132	1389	909	1091	938	1194	773	958	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901957QAC1	50	386.6		1531	1183	1393	1090	1250	992	1099	887	1422	1127	1337	1068	1160	1410	944	1126	971	1223	809	995	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901957RAC1	60	408.3		1617	1249	1472	1151	1320	1047	1160	936	1502	1190	1412	1128	1225	1489	997	1189	1025	1291	854	1050	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901958QAC1	50	435.6		1686	1328	1544	1230	1395	1126	1237	1014	1579	1275	1491	1213	1307	1569	1081	1276	1117	1375	935	1137	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901958RAC1	60	461.9		1787	1408	1637	1305	1479	1194	1312	1076	1674	1352	1581	1286	1386	1664	1147	1353	1174	1458	991	1206	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901959RAC1	60	482.6		1840	1467	1691	1364	1535	1254	1369	1136	1734	1417	1642	1352	1448	1726	1212	1421	1238	1522	1057	1274	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901959SAC1	80	533.4		2027	1621	1865	1509	1695	1389	1514	1259	1911	1566	1811	1495	1600	1903	1343	1571	1370	1681	1172	1411	
MCW Series	2 ft (0.6 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901959TAC1	100	564.4		2148	1716	1976	1596	1794	1469	1612	1323	2025	1657	1918	1582	1693	2016	1420	1662	1449	1719	1240	1492	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901116BCR1	1.5	16.9		68	52	62	48	55	44	48	39	63	49	59	47	51	62	41	49	42	54	35	43	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901116CCR1	2	18.8		76	58	69	53	61	48	54	43	70	55	66	52	56	69	45	54	47	59	39	48	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901116DCR1	3	21.6		87	67	79	61	71	55	62	49	80	63	75	59	65	79	52	63	54	68	44	55	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901117DCR1	3	24.5		96	75	88	69	79	63	70	56	90	71	84	68	73	89	60	71	62	77	51	63	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901117FCR1	5	29.2		115	89	105	82	94	75	83	67	107	85	101	81	87	106	71	85	73	92	61	75	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901126FCR1	5	42.3		171	130	155	119	138	108	121	96	157	123	147	116	127	155	102	123	105	134	87	108	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901126HCR1	7.5	47		190	145	172	133	153	120	134	107	175	137	164	129	141	173	113	136	117	149	96	120	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901127HCR1	7.5	53.6		211	164	193	151	173	139	152	123	197	156	185	148	161	195	131	156	135	169	112	138	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901127JCR1	10	65.3		230	175	210	165	188	150	166	134	214	170	201	167	175	216	143	170	147	184	122	150	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901136HCR1	7.5	62.1		251	191	227	175	203	159	177	141	231	180	216	171	186	228	150	180	155	196	128	158	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901136JCR1	10	70.6		285	217	258	199	230	180	201	160	262	205	246	194	212	259	170	204	176	223	145	179	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901137HCR1	7.5	70.6		279	216	254	199	228	181	201	162	259	206	244	195	212	257	173	205	177	223	148	182	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901137JCR1	10	80		315	245	287	226	258	205	227	184	293	233	276	221	240	291	196	233	201	253	168	206	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901137KCR1	15	87.5		345	268	315	247	283	225	249	201	321	255	302	242	262	318	214	255	220	277	183	225	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901146KCR1	15	96		387	295	351	271	313	245	274	218	357	279	334	263	288	353	231	278	239	304	197	244	
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901147KCR1</																								

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT/LWT	90	95	90	95	90	95	90	95	95	100	95	100	95	97	100	102	95	97	100	102
						80	80	80	80	80	80	80	80	80	80	80	80	80	85	85	85	85	87	87	87
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901757RCR1	60	411.1		1619	1258	1476	1160	1327	1057	1169	946	1506	1199	1418	1137	1233	1493	1007	1198	1035	1299	863	1060
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901758RCR1	60	441.2		1697	1245	1567	1248	1410	1143	1255	1032	1292	1506	1231	1137	1324	1582	1099	1283	1125	1391	953	1165
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901946NCR1	30	236.1		954	726	864	666	770	603	673	537	878	696	822	648	708	868	570	683	588	747	485	600
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901946PCR1	40	258.7		1046	795	947	729	844	660	737	587	963	751	902	710	776	952	624	749	643	818	530	657
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901947NCR1	30	263.4		1040	806	947	743	851	676	749	606	967	768	909	728	790	958	644	767	662	832	552	679
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901947PCR1	40	290.7		1148	889	1046	820	939	746	827	668	1067	848	1004	804	872	1058	711	847	731	919	609	749
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901948NCR1	30	288.8		1114	880	1022	816	924	748	821	674	1045	846	987	805	866	1038	718	846	735	911	621	755
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901948PCR1	40	319.8		1233	975	1131	904	1023	828	909	747	1156	936	1093	892	960	1149	796	937	815	1009	689	837
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901949PCR1	40	336.8		1279	1024	1177	953	1070	877	956	796	1206	989	1143	944	1010	1201	848	992	866	1061	741	891
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901949QCR1	50	365.9		1388	1112	1278	1036	1162	954	1039	866	1309	1075	1241	1026	1098	1303	923	1078	942	1153	806	969
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901949RCR1	60	391.3		1480	1189	1364	1108	1242	1022	1112	928	1397	1150	1326	1098	1174	1391	988	1153	1008	1232	865	1037
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901956QCR1	50	352.8		1428	1085	1292	995	1151	901	1005	802	1313	1025	1230	968	1058	1298	851	1021	878	1116	724	897
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901956RCR1	60	377.2		1528	1160	1382	1064	1231	963	1075	857	1405	1095	1316	1035	1132	1389	909	1091	938	1194	773	958
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901957QCR1	50	386.6		1531	1183	1393	1090	1250	992	1099	887	1422	1127	1337	1068	1160	1410	944	1126	971	1223	809	995
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901957RCR1	60	408.3		1617	1249	1472	1151	1320	1047	1160	936	1502	1190	1412	1128	1225	1489	997	1189	1025	1291	854	1050
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901958QCR1	50	435.6		1686	1328	1544	1230	1395	1126	1237	1014	1579	1275	1491	1213	1307	1569	1081	1276	1107	1375	935	1137
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901958RCR1	60	461.9		1787	1408	1637	1305	1479	1194	1312	1076	1674	1352	1581	1286	1386	1664	1147	1353	1174	1458	991	1206
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901959RCR1	60	482.6		1840	1467	1691	1364	1535	1254	1369	1136	1734	1417	1642	1352	1448	1726	1212	1421	1238	1522	1057	1274
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901959SCR1	80	533.4		2027	1621	1865	1509	1695	1389	1514	1259	1911	1586	1811	1495	1690	1903	1343	1571	1370	1681	1172	1411
MCW Series	4 ft (1.2 m) Inlet Attenuators	MCW901959TCR1	100	584.4		2148	1716	1976	1596	1794	1469	1602	1332	2025	1657	1918	1582	1693	2016	1420	1662	1449	1779	1240	1492
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901116BCA1	1.5	16.9		68	52	62	48	55	43	48	39	63	49	59	47	51	62	41	49	42	54	35	43
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901116CCA1	2	18.8		76	58	69	53	61	48	54	43	70	55	66	52	56	69	45	54	47	59	39	48
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901116DCA1	3	21.6		87	67	79	61	71	55	62	49	80	63	75	59	65	79	52	63	54	68	44	55
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901117DCA1	3	24.5		96	75	88	69	79	63	70	56	90	71	84	68	73	89	60	71	62	77	51	63
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901117FCA1	5	29.2		115	89	105	82	94	75	83	67	107	85	101	81	87	106	71	85	73	92	61	75
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901126FCA1	5	42.3		171	130	155	119	138	108	121	96	157	123	147	116	127	155	102	123	105	134	87	108
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901126HCA1	7.5	47		190	145	172	133	153	120	134	107	175	137	164	129	141	173	113	136	117	149	96	120
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901127HCA1	7.5	53.6		211	164	193	151	173	138	152	123	197	156	185	148	161	195	131	156	135	169	112	138
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901127JCA1	10	58.3		230	178	210	165	188	150	166	134	214	170	201	161	175	212	143	170	147	184	122	150
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901136HCA1	7.5	62.1		251	191	227	175	203	159	177	141	231	180	216	171	186	228	150	180	155	196	128	158
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901136JCA1	10	70.6		285	217	258	199	230	180	201	160	262	205	246	194	212	259	170	204	176	223	145	179
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901137HCA1	7.5	70.6		279	216	254	199	228	181	201	162	259	206	244	195	212	257	173	205	177	223	148	182
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901137JCA1	10	80.7		315	245	287	226	258	205	227	184	293	233	276	221	240	291	196	233	201	253	168	206
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901137KCA1	15	87.5		345	268	315	247	283	225	249	201	321	255	302	242	262	318	214	255	220	277	183	225
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901146KCA1	15	96		387	295	351	271	313	245	274	218	357	279	334	263	288	353	231	278	239	304	197	244
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901147KCA1	15	110.1		434	337	395	311	355	283	333	253	403	321	380	304	330	400	269	321	277	348	231	284
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901147LCA1	20	117.3		484	360	433	333	380	302	334	270	432	343	406	325	353	428	287	342	296	372	246	303
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901156KCA1	15	126.1		509	388	461	356	411	322	359	287	468	366	439	346	378	463	304	365	314	399	259	321
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901156LCA1	20	141.1		570	434	516	398	460	360	402	321	524	410	491	387	423	518	348	408	351	446	289	359
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901157LCA1	20	159.9		630	489	575	451	516	411	455	367	586	466	552	442	480	581	391	466	402	505	335	412
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901157NCA1	30	175.9		695	538	633	496	568	451	500	404	646	513	608	486	528	640	430	512	442	556	368	453
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901546MCA1	25	201.3		805	619	732	569	655	514	575	460	743	585	698	554	604	735	488	583	503	636	415	514
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901546NCA1	30	211.7		846	650	769	598	689	543	604	483	781	615	734	582	635	773	513	613	529	668	436	540
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901547MCA1	25	224.8		875	687	802	636	724	581	641	521	817	656	771	624	675	810	554	656	569	709	476	583
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators																								

Capacity Represented in Water Flow (gpm)

- [1] Water flow above maximum allowed for this model, maximum shown
- [2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT/LWT	90	95	90	95	90	95	90	95	90	95	100	95	100	95	97	100	102	95	97	100	102
						80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	85	85	85	85	85	85
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901949PCA1	40	336.8	1279	1024	1177	953	1070	877	956	796	1206	989	1143	944	1010	1201	848	992	866	1061	741	891		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901949OCA1	60	324.9	1388	1112	1278	1036	1122	954	1036	826	1309	1076	1241	1054	1098	1303	923	1058	943	1153	806	969		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901949RCA1	60	391.3	1480	1189	1364	1108	1242	1022	1112	922	1309	1076	1241	1054	1098	1303	923	1058	943	1153	806	969		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901956QCA1	50	352.9	1428	1085	1292	995	1151	901	1005	802	1313	1025	1230	968	1058	1298	851	1021	878	1116	724	897		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901956RCA1	60	377.2	1528	1160	1382	1064	1231	963	1075	857	1405	1095	1316	1035	1132	1389	909	1091	938	1194	773	958		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901957QCA1	50	386.6	1531	1183	1393	1090	1250	992	1099	887	1422	1127	1337	1068	1160	1410	944	1126	971	1223	809	995		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901957RCA1	60	408.3	1617	1249	1472	1151	1320	1047	1160	936	1502	1190	1412	1128	1225	1489	997	1189	1025	1291	854	1050		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901958QCA1	50	435.6	1686	1328	1544	1230	1395	1126	1237	1014	1579	1275	1491	1213	1307	1569	1081	1276	1107	1375	935	1137		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901958RCA1	60	461.9	1787	1408	1637	1305	1479	1194	1312	1076	1674	1352	1581	1286	1386	1664	1147	1353	1174	1458	991	1206		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901959RCA1	60	482.6	1840	1467	1691	1364	1535	1254	1369	1136	1734	1417	1642	1352	1448	1726	1212	1421	1238	1522	1057	1274		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901959SCA1	80	533.4	2027	1621	1865	1509	1695	1389	1514	1259	1911	1566	1811	1495	1600	1903	1343	1571	1370	1681	1172	1411		
MCW Series	4 ft (1.2 m) Inlet & 2 ft (0.6 m) Outlet Attenuators	MCW901959TCA1	100	564.4	2148	1716	1976	1596	1794	1469	1602	1332	2025	1657	1918	1582	1693	2016	1420	1662	1449	1779	1240	1492		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901116BCC1	1.5	16.9	68	52	62	48	55	43	48	39	63	49	59	47	51	62	41	49	42	54	35	43		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901116CCC1	2	18.8	76	58	69	53	61	48	54	43	70	55	66	52	56	69	45	54	47	59	39	48		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901116DCC1	3	21.6	87	67	79	61	71	55	62	49	80	63	75	59	65	79	52	63	54	68	44	55		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901117DCC1	3	24.5	96	75	88	69	79	63	70	56	90	71	84	68	73	89	60	71	62	77	51	63		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901117FCC1	5	29.2	115	89	105	82	94	75	83	67	107	85	101	81	87	106	71	85	73	92	61	75		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901126FCC1	5	42.3	171	130	155	119	138	108	121	96	157	123	147	116	127	155	102	123	105	134	87	108		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901126HCC1	7.5	47	190	145	172	133	153	120	134	107	175	137	164	129	141	173	113	136	117	149	96	120		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901127HCC1	7.5	53.6	211	164	193	151	173	138	152	123	197	156	185	148	161	195	131	156	135	169	112	138		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901127JCC1	10	58.3	230	178	210	165	188	150	166	134	214	170	201	161	175	212	143	170	147	184	122	150		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901136HCC1	7.5	62.1	251	191	227	175	203	159	177	141	231	180	216	171	186	228	150	180	155	196	128	158		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901136JCC1	10	70.6	285	217	258	199	230	180	201	160	262	205	246	194	212	259	170	204	176	223	145	179		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901137HCC1	7.5	70.6	279	216	254	199	228	181	201	162	259	206	244	195	212	257	173	205	177	223	148	182		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901137JCC1	10	80	315	245	287	226	258	205	227	184	293	233	276	221	240	291	196	233	201	253	168	206		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901137KCC1	15	87.5	345	268	315	247	283	225	249	201	321	255	302	242	262	318	214	255	220	277	183	225		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901146KCC1	15	96	387	295	351	271	313	245	274	218	357	279	334	263	288	353	231	278	239	304	197	244		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901147KCC1	15	110.1	434	337	395	311	355	283	313	253	403	321	380	304	330	400	269	321	277	348	231	284		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901147LCC1	20	117.6	464	360	423	332	380	304	320	270	432	343	406	325	353	428	287	342	296	372	246	303		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901156KCC1	15	126.1	509	388	461	356	411	322	359	287	468	366	439	346	378	463	304	365	314	399	259	321		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901156LCC1	20	141.1	570	434	516	398	460	360	402	321	524	410	491	387	423	518	340	408	351	446	289	359		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901157LCC1	20	159.9	630	489	575	451	516	411	455	367	586	466	552	442	480	581	391	466	402	505	335	412		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901157NCC1	30	175.9	695	538	633	496	568	451	500	404	646	513	608	486	528	640	430	512	442	556	368	453		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901546MCC1	25	201.3	805	619	732	569	655	516	575	460	743	585	698	554	604	735	488	583	503	636	415	514		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901546NCC1	30	211.7	846	650	769	598	689	543	604	483	781	615	734	582	635	773	513	613	529	668	436	540		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901547MCC1	25	224.8	876	687	802	636	724	581	641	521	817	656	771	624	675	810	554	656	569	709	476	583		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901547NCC1	30	238.0	928	728	843	706	815	615	652	562	864	695	816	660	714	857	597	694	622	750	506	617		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901548NCC1	30	254	966	774	890	720	810	663	724	600	909	745	862	711	762	903	637	745	652	799	554	669		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901548PCC1	40	280.3	1040	811	954	785	894	731	799	662	1004	822	952	784	841	998	704	823	720	882	612	738		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901549PCC1	40	290.7	1040	811	954	785	894	731	799	662	1004	822	952	784	841	998	704	823	720	882	612	738		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901556NCC1	30	269	1080	827	981	760	876	689	767	613	936	782	935	740	807	985	651	779	671	850	554	685		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901556PCC1	40	296.3	1190	911	1080	836	965	758	845	675	1097	861	1030	815	889	1085	716	858	739	937	609	755		
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901556QCC1	50	316.1	1270	971	1152	892	1030	809	902	720	1171	91												

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT LWT WB	90	95	90	95	90	95	90	95	90	95	100	95	100	95	97	100	102	95	97	100	102
						80	80	80	80	80	80	80	80	80	85	85	85	85	85	85	85	85	87	85	87	87
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901958RCC1	60	461.9		1787	1408	1637	1305	1479	1194	1312	1076	1674	1352	1581	1286	1386	1664	1147	1353	1174	1458	991	1206	
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901959RCC1	60	482.6		1840	1467	1691	1364	1535	1254	1369	1136	1734	1417	1642	1352	1448	1726	1212	1421	1238	1522	1057	1274	
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901959SCC1	80	533.4		2027	1621	1865	1509	1695	1389	1514	1259	1911	1566	1611	1495	1600	1903	1343	1571	1370	1681	1172	1411	
MCW Series	4 ft (1.2 m) Inlet & 4 ft (1.2 m) Outlet Attenuators	MCW901959TCC1	100	564.4		2148	1716	1976	1596	1794	1469	1602	1332	2025	1657	1918	1582	1693	2016	1420	1662	1449	1779	1240	1492	