

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT																				
					80	80	90	95	90	95	90	95	90	95	100	95	97	100	102	95	97	100	102		
					LWT	80	80	90	95	90	95	90	95	90	95	100	95	97	100	102	95	97	100	102	
					WB	66	66	68	68	70	70	72	72	75	75	76	76	78	78	78	78	80	80	80	80
MD	Inline Standard Low Sound (A)	MDS008MAC1L	7.5	165		638	506	587	468	533	428	473	384	595	481	564	457	495	590	406	479	418	519	[2]	426
MD	Inline Standard Low Sound (A)	MDS008MAD1L	7.5	180		682	549	631	511	576	469	515	423	642	527	610	502	540	638	449	526	460	565	387	471
MD	Inline Standard Low Sound (A)	MDS008MAF1L	7.5	189		704	575	654	537	600	496	540	450	667	555	635	531	567	663	478	555	488	593	416	501
MD	Inline Standard Low Sound (A)	MDS008NAC1L	10	179		692	549	637	508	578	465	513	417	646	522	611	496	537	639	441	520	453	562	378	462
MD	Inline Standard Low Sound (A)	MDS008NAD1L	10	197		745	601	690	560	630	514	564	464	702	576	667	550	591	697	492	576	504	618	425	516
MD	Inline Standard Low Sound (A)	MDS008NAF1L	10	207		768	630	715	589	657	544	592	494	728	608	695	582	621	725	524	608	536	649	457	549
MD	Inline Standard Low Sound (A)	MDS008PAC1L	15	202		779	619	718	574	652	525	579	471	728	589	689	560	606	721	498	587	512	635	427	522
MD	Inline Standard Low Sound (A)	MDS008PAD1L	15	223		838	680	778	634	712	584	639	527	791	653	752	624	669	785	559	652	573	699	483	586
MD	Inline Standard Low Sound (A)	MDS008PAF1L	15	234		862	712	804	667	741	618	670	562	819	688	782	659	702	814	596	688	609	732	521	623
MD	Inline Standard Low Sound (A)	MDS008QAC1L	20	216		829	662	765	[2]	696	[2]	[2]	[2]	775	[2]	735	[2]	648	768	[2]	[2]	[2]	678	[2]	[2]
MD	Inline Standard Low Sound (A)	MDS008QAD1L	20	239		895	729	831	681	762	627	685	568	844	700	804	669	717	839	601	699	616	749	520	629
MD	Inline Standard Low Sound (A)	MDS008QAF1L	20	255		937	775	874	728	806	675	731	615	890	750	851	719	765	885	651	750	665	797	570	681
MD	Inline Standard Low Sound (A)	MDS010PAC1L	15	248		962	760	885	704	801	642	710	575	897	723	849	687	744	888	609	720	627	780	520	639
MD	Inline Standard Low Sound (A)	MDS010PAD1L	15	279		1057	852	978	792	893	727	798	655	995	816	945	778	837	988	695	815	713	876	599	730
MD	Inline Standard Low Sound (A)	MDS010PAF1L	15	293		1088	891	1012	834	930	770	838	699	1031	860	983	823	879	1026	742	861	758	918	646	777
MD	Inline Standard Low Sound (A)	MDS010QAC1L	20	269		1041	825	958	764	868	698	771	625	971	784	919	745	807	962	662	782	681	845	566	695
MD	Inline Standard Low Sound (A)	MDS010QAD1L	20	304		1144	927	1061	865	971	795	871	718	1078	890	1026	850	912	1071	761	889	780	953	657	798
MD	Inline Standard Low Sound (A)	MDS010QAF1L	20	317		1170	964	1090	903	1024	836	908	766	1110	931	1060	892	951	1105	806	932	824	992	704	844
MD	Inline Standard Low Sound (A)	MDS010RAC1L	25	286		1102	876	1016	813	922	743	820	666	1029	834	975	793	858	1020	705	831	726	898	604	740
MD	Inline Standard Low Sound (A)	MDS010RAD1L	25	325		1219	991	1131	925	1037	852	932	770	1150	952	1095	909	975	1142	816	951	836	1018	706	855
MD	Inline Standard Low Sound (A)	MDS010RAF1L	25	341		1255	1037	1171	972	1079	901	977	820	1192	1002	1139	961	1023	1186	869	1003	888	1067	760	909
MD	Inline Standard Low Sound (A)	MDS010SAF1L	30	360		1327	1095	1237	1026	1140	951	1031	866	1260	1058	1203	1014	1080	1254	917	1059	937	1126	802	959
MD	Inline Standard Low Sound (A)	MDS016PAC1L	15	317		1231	972	1132	899	1025	821	908	735	1147	924	1085	878	951	1136	778	921	801	997	665	817
MD	Inline Standard Low Sound (A)	MDS016PAD1L	15	350		1330	1069	1230	993	1121	911	1001	820	1251	1024	1188	975	1050	1242	871	1023	893	1100	750	914
MD	Inline Standard Low Sound (A)	MDS016PAF1L	15	368		1372	1120	1275	1046	1169	965	1051	874	1300	1080	1238	1033	1104	1293	929	1081	950	1154	808	974
MD	Inline Standard Low Sound (A)	MDS016QAC1L	20	345		1338	1058	1231	979	1115	984	988	800	1248	1005	1180	955	1035	1236	847	1002	872	1085	724	889
MD	Inline Standard Low Sound (A)	MDS016QAD1L	20	383		1452	1169	1343	1087	1225	998	1095	899	1366	1120	1298	1068	1149	1357	954	1119	979	1203	823	1001
MD	Inline Standard Low Sound (A)	MDS016QAF1L	20	403		1497	1226	1393	1146	1279	1059	1152	961	1419	1183	1353	1132	1209	1412	1020	1184	1042	1263	888	1068
MD	Inline Standard Low Sound (A)	MDS016RAC1L	25	369		1429	1131	1315	1047	1192	956	1057	857	1333	1075	1261	1022	1107	1320	907	1072	934	1160	776	952
MD	Inline Standard Low Sound (A)	MDS016RAD1L	25	410		1549	1251	1435	1165	1310	1071	1173	966	1459	1200	1387	1145	1230	1448	1024	1199	1050	1287	884	1074
MD	Inline Standard Low Sound (A)	MDS016RAF1L	25	431		1593	1311	1485	1228	1366	1136	1234	1032	1512	1266	1443	1213	1293	1504	1094	1267	1118	1350	955	1146
MD	Inline Standard Low Sound (A)	MDS016SAC1L	30	390		1511	1196	1390	1107	1260	1011	1118	905	1409	1137	1333	1080	1170	1395	958	1133	986	1226	819	1006
MD	Inline Standard Low Sound (A)	MDS016SAD1L	30	436		1646	1330	1524	1239	1393	1139	1248	1028	1550	1276	1474	1218	1308	1539	1090	1275	1118	1368	940	1143
MD	Inline Standard Low Sound (A)	MDS016SAF1L	30	460		1702	1399	1585	1310	1458	1212	1317	1101	1614	1351	1541	1294	1380	1606	1168	1352	1194	1440	1019	1223
MD	Inline Standard Low Sound (A)	MDS016TAD1L	40	475		1788	1449	1657	1351	1516	1244	1361	1123	1685	1391	1603	1328	1425	1673	1190	1389	1200	1489	1029	1247
MD	Inline Standard Low Sound (A)	MDS016TAF1L	40	500		1847	1520	1721	1425	1584	1319	1432	1201	1753	1469	1673	1408	1500	1743	1272	1470	1300	1565	1112	1331
MD	Inline Standard Low Sound (A)	MDS018QAC1L	20	470		1818	1441	1674	1334	1518	1219	1347	1092	1697	1370	1606	1302	1410	1680	1155	1365	1189	1477	989	1213
MD	Inline Standard Low Sound (A)	MDS018QAD1L	20	516		1953	1575	1808	1466	1650	1346	1476	1213	1839	1510	1747	1440	1548	1826	1287	1508	1320	1620	1110	1350
MD	Inline Standard Low Sound (A)	MDS018QAF1L	20	540		2007	1643	1867	1536	1714	1418	1544	1286	1903	1585	1814	1517	1620	1893	1366	1587	1396	1693	1189	1431
MD	Inline Standard Low Sound (A)	MDS018RAC1L	25	500		1932	1533	1779	1420	1614	1297	1433	1163	1803	1458	1707	1386	1500	1786	1230	1453	1266	1571	1053	1291
MD	Inline Standard Low Sound (A)	MDS018RAD1L	25	552		2085	1685	1932	1568	1765	1441	1580	1300	1964	1615	1867	1541	1656	1950	1378	1614	1414	1732	1190	1446
MD	Inline Standard Low Sound (A)	MDS018RAF1L	25	575		2133	1749	1986	1636	1824	1512	1644	1372	2023	1688	1930	1616	1725	2012	1456	1690	1488	1802	1269	1525
MD	Inline Standard Low Sound (A)	MDS018SAC1L	30	528		2040	1619	1879	1499	1704	1370	1514	1228	1904	1539	1803	1463	1584	1886	1299	1534	1337	1659	1112	1364
MD	Inline Standard Low Sound (A)	MDS018SAD1L	30	586		2213	1788	2050	1665	1873	1530	1677	1380	2085	1715	1982	1636	1758	2070	1463	1713	1501	1839	1264	1535
MD	Inline Standard Low Sound (A)	MDS018SAF1L	30	615		2280	1871	2123	1750	1951	1617	1759	1468	2163	1806	2063	1729	1845	2151	1558	1807	1592	1927	1359	1632
MD	Inline Standard Low Sound (A)	MDS018TAC1L	40	580		2240	1778	2063	1647	1872	1505	1663	1348	2091	1691	1980	1608	1740	2071	1427	1685	1469	1823	1221	1498
MD	Inline Standard Low Sound (A)	MDS0																							

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT																			
					LWT	WB	90 80	95 80	90 80	95 80	90 80	95 80	90 80	95 80	90 80	95 80	90 80	95 80	100 80	95 80	97 80	100 80	95 80	97 80
MD	Inline Quiet Fan (L)	MDS016PLCL1	15	320	1240	981	1141	908	1034	829	917	743	1157	933	1094	886	960	1145	786	930	809	1006	673	825
MD	Inline Quiet Fan (L)	MDS016PLDL1	15	353	1338	1078	1238	1002	1130	920	1010	829	1259	1033	1196	984	1059	1250	879	1032	902	1109	759	923
MD	Inline Quiet Fan (L)	MDS016PFL1L	15	370	1376	1126	1280	1052	1175	971	1057	881	1304	1086	1243	1039	1110	1297	935	1087	956	1160	815	980
MD	Inline Quiet Fan (L)	MDS016QLCL1	20	348	1342	1067	1237	988	1123	904	998	810	1254	1015	1187	965	1044	1242	857	1011	882	1093	735	899
MD	Inline Quiet Fan (L)	MDS016QLDL1	20	384	1448	1172	1342	1092	1227	1004	1099	906	1365	1124	1298	1073	1152	1355	960	1123	985	1205	830	1007
MD	Inline Quiet Fan (L)	MDS016QLFL1	20	401	1483	1220	1382	1142	1271	1056	1147	960	1408	1178	1344	1128	1203	1400	1018	1179	1040	1256	889	1066
MD	Inline Quiet Fan (L)	MDS016RCL1L	25	372	1435	1140	1322	1057	1200	966	1067	866	1340	1085	1269	1032	1116	1327	916	1081	943	1169	785	962
MD	Inline Quiet Fan (L)	MDS016RDL1L	25	412	1549	1257	1437	1172	1315	1078	1180	974	1461	1206	1390	1152	1236	1451	1032	1205	1058	1292	893	1082
MD	Inline Quiet Fan (L)	MDS016RFL1L	25	431	1585	1310	1479	1229	1364	1139	1235	1037	1506	1267	1439	1214	1293	1498	1098	1268	1122	1348	960	1149
MD	Inline Quiet Fan (L)	MDS016SCL1L	30	394	1518	1207	1399	1119	1271	1024	1130	918	1418	1149	1343	1093	1182	1405	971	1145	1000	1237	832	1019
MD	Inline Quiet Fan (L)	MDS016SDL1L	30	437	1637	1333	1521	1244	1394	1146	1253	1036	1545	1280	1472	1223	1311	1535	1097	1279	1125	1369	949	1150
MD	Inline Quiet Fan (L)	MDS016SFL1L	30	459	1686	1395	1574	1309	1452	1214	1316	1105	1602	1349	1532	1294	1377	1594	1171	1350	1196	1435	1024	1224
MD	Inline Quiet Fan (L)	MDS016TDL1L	40	471	1757	1436	1634	1342	1500	1239	1352	1122	1660	1380	1582	1320	1413	1648	1187	1379	1216	1474	1030	1242
MD	Inline Quiet Fan (L)	MDS016TFL1L	40	493	1806	1498	1687	1408	1558	1307	1414	1192	1717	1450	1643	1391	1479	1709	1261	1451	1288	1541	1106	1318
MD	Inline Quiet Fan (L)	MDS018NCL1L	10	376	1454	1153	1339	1068	1214	976	1078	875	1357	1096	1285	1042	1128	1344	925	1092	952	1182	793	971
MD	Inline Quiet Fan (L)	MDS018NDL1L	10	406	1540	1239	1424	1153	1299	1058	1161	954	1449	1188	1376	1132	1218	1438	1012	1186	1038	1275	873	1062
MD	Inline Quiet Fan (L)	MDS018NFL1L	10	422	1574	1284	1462	1199	1340	1106	1206	1003	1491	1239	1420	1184	1266	1482	1065	1240	1089	1324	927	1117
MD	Inline Quiet Fan (L)	MDS018PCL1L	15	428	1654	1312	1523	1215	1382	1110	1227	896	1544	1248	1462	1204	1284	1529	1053	1244	1084	1345	903	1105
MD	Inline Quiet Fan (L)	MDS018PDL1L	15	466	1764	1422	1633	1324	1490	1216	1333	1096	1644	1363	1578	1300	1388	1649	1162	1362	1192	1463	1003	1219
MD	Inline Quiet Fan (L)	MDS018PFL1L	15	485	1804	1476	1678	1379	1540	1273	1386	1155	1710	1424	1630	1362	1455	1701	1226	1425	1253	1521	1067	1285
MD	Inline Quiet Fan (L)	MDS018QLCL1L	20	461	1777	1413	1638	1310	1487	1198	1322	1074	1660	1344	1572	1279	1383	1644	1136	1340	1169	1448	974	1192
MD	Inline Quiet Fan (L)	MDS018QLDL1L	20	506	1908	1544	1769	1438	1617	1322	1449	1193	1798	1481	1710	1413	1518	1786	1265	1479	1297	1587	1093	1326
MD	Inline Quiet Fan (L)	MDS018QLFL1L	20	530	1963	1612	1829	1509	1681	1394	1516	1266	1863	1556	1777	1490	1590	1853	1343	1558	1373	1661	1172	1407
MD	Inline Quiet Fan (L)	MDS018RCL1L	25	492	1897	1508	1749	1398	1587	1278	1411	1146	1772	1425	1679	1364	1476	1755	1212	1430	1247	1546	1038	1272
MD	Inline Quiet Fan (L)	MDS018RDL1L	25	543	2048	1657	1898	1543	1735	1419	1554	1280	1930	1589	1835	1516	1629	1916	1357	1588	1392	1704	1173	1423
MD	Inline Quiet Fan (L)	MDS018RFL1L	25	566	2097	1722	1953	1611	1795	1489	1619	1352	1990	1662	1898	1591	1698	1979	1434	1664	1466	1773	1251	1502
MD	Inline Quiet Fan (L)	MDS018SCL1L	30	519	2000	1591	1843	1475	1674	1348	1488	1209	1868	1513	1770	1440	1557	1850	1279	1509	1316	1630	1096	1342
MD	Inline Quiet Fan (L)	MDS018SDL1L	30	576	2169	1757	2012	1638	1840	1506	1649	1360	2045	1686	1945	1609	1728	2031	1441	1684	1478	1807	1246	1511
MD	Inline Quiet Fan (L)	MDS018SFL1L	30	603	2230	1834	2078	1717	1911	1588	1725	1443	2117	1771	2020	1696	1809	2106	1530	1773	1564	1889	1336	1602
MD	Inline Quiet Fan (L)	MDS018TCL1L	40	569	2191	1744	2020	1617	1835	1479	1632	1326	2047	1659	1940	1578	1707	2028	1403	1654	1444	1787	1202	1472
MD	Inline Quiet Fan (L)	MDS018TDL1L	40	632	2378	1928	2206	1797	2018	1653	1810	1492	2243	1850	2134	1766	1896	2227	1581	1848	1622	1982	1367	1658
MD	Inline Quiet Fan (L)	MDS018TFL1L	40	663	2450	2017	2284	1888	2101	1746	1897	1587	2326	1947	2221	1865	1989	2314	1682	1949	1719	2076	1469	1761
MD	Inline Quiet Fan (L)	MDS018UDL1L	50	678	2550	2069	2366	1928	2165	1773	1942	1601	2405	1985	2289	1894	2034	2388	1696	1983	1740	2126	1467	1778
MD	Inline Quiet Fan (L)	MDS018ULFL1L	50	710	2622	2159	2445	2022	2250	1871	2032	1701	2490	2086	2377	1998	2130	2477	1803	2087	1842	2223	1576	1887
MD	Inline Quiet Fan (L)	MDS018VFL1L	60	740	2735	2251	2549	2108	2345	1950	2118	1774	2596	2174	2478	2082	2220	2582	1880	2176	1921	2317	1644	1968
MD	Inline Ultra Quiet Fan (C)	MDS008KCC1L	5	151	582	463	536	429	487	393	433	[2]	543	440	515	419	453	538	373	439	383	474	[2]	391
MD	Inline Ultra Quiet Fan (C)	MDS008KCD1L	5	164	620	500	574	466	524	428	466	386	584	480	555	458	492	580	410	479	420	515	[2]	430
MD	Inline Ultra Quiet Fan (C)	MDS008KCF1L	5	170	632	517	588	484	540	446	486	405	599	499	571	478	510	596	430	500	440	533	375	451
MD	Inline Ultra Quiet Fan (C)	MDS008MCC1L	7.5	165	634	506	585	469	532	430	474	386	593	481	562	458	495	587	408	480	420	518	[2]	428
MD	Inline Ultra Quiet Fan (C)	MDS008MCD1L	7.5	180	677	549	628	512	575	471	516	425	639	527	608	503	540	634	451	526	462	564	390	472
MD	Inline Ultra Quiet Fan (C)	MDS008MCF1L	7.5	189	699	575	652	538	599	498	541	452	664	555	633	532	567	660	480	556	490	592	419	502
MD	Inline Ultra Quiet Fan (C)	MDS008NCC1L	10	179	688	548	635	509	577	466	514	418	643	522	610	497	537	637	442	520	455	562	379	464
MD	Inline Ultra Quiet Fan (C)	MDS008NCD1L	10	197	742	601	688	560	629	515	564	466	699	577	665	551	591	694	493	576	506	618	427	517
MD	Inline Ultra Quiet Fan (C)	MDS008NCF1L	10	207	766	630	713	590	656	545	592	496	727	608	693	582	621	723	525	609	537	648	459	550
MD	Inline Ultra Quiet Fan (C)	MDS008PCC1L	15	202	774	619	715	575	650	526	580	473	724	589	687	561	606	718	500	588	514	634	429	524
MD	Inline Ultra Quiet Fan (C)	MDS008PCD1L	15	223	837	680	777	635	712	584	639	528	790	653	752	624	669	784	559	652	573	699	484	586
MD	Inline Ultra Quiet Fan (C)	MDS008PCFL1L	15	234	863	712	805	667	741	617	670	561	819	687	783	659	702	815	595	688	608	732	520	622
MD	Inline Ultra Quiet Fan (C)	MDS008QCC1L	20	216	829	662	765	[2]	696	[2]	[2]	[2												

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT		90		95		100		95		100		95		97		100		95		97		100		95		97		100					
					LWT	WB	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	80	
MD	Inline Quiet Fan Splash Attenuation (J)	MDS018TJC1L	40	569	2191	1744	2020	1617	1835	1479	1632	1326	2047	1659	1940	1578	1707	2028	1403	1654	1444	1870	1202	1472														
MD	Inline Quiet Fan Splash Attenuation (J)	MDS018TJD1L	40	632	2378	1928	2206	1797	2018	1653	1810	1492	2243	1850	2134	1766	1896	2227	1581	1848	1622	1982	1367	1658														
MD	Inline Quiet Fan Splash Attenuation (J)	MDS018TJF1L	40	632	2450	2017	2284	1888	2101	1746	1897	1587	2326	1947	2221	1865	1989	2314	1682	1949	1719	2076	1469	1761														
MD	Inline Quiet Fan Splash Attenuation (J)	MDS018UJD1L	50	678	2550	2069	2366	1928	2165	1773	1942	1601	2405	1985	2289	1894	2034	2388	1696	1983	1740	2126	1467	1778														
MD	Inline Quiet Fan Splash Attenuation (J)	MDS018UJF1L	50	710	2622	2159	2445	2022	2250	1871	2032	1701	2490	2086	2377	1998	2130	2477	1803	2087	1842	2233	1576	1887														
MD	Inline Quiet Fan Splash Attenuation (J)	MDS018VJF1L	60	740	2735	2251	2549	2108	2345	1950	2118	1774	2596	2174	2478	2082	2220	2582	1880	2176	1921	2317	1644	1968														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008KCC1L	5	151	582	462	536	429	487	393	433	[2]	543	440	515	419	453	538	373	439	383	474	[2]	391														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008KCD1L	5	164	620	500	574	466	524	428	469	386	584	480	555	458	492	580	410	479	420	515	[2]	430														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008KCF1L	5	170	632	517	588	484	540	446	486	405	599	499	571	478	510	596	430	500	440	533	375	451														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008MKC1L	7.5	165	634	506	585	469	532	430	474	386	593	481	562	458	495	587	408	480	420	518	[2]	428														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008MKD1L	7.5	180	677	549	628	512	575	471	516	425	639	527	608	503	540	634	451	526	462	564	390	470														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008MKF1L	7.5	189	699	575	652	538	599	498	541	452	664	555	633	532	567	660	480	556	490	592	419	502														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008NK1L	10	179	688	548	635	509	577	466	514	418	643	522	610	497	537	637	442	520	455	562	379	464														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008NKD1L	10	197	742	601	688	560	629	515	564	466	699	577	665	551	591	694	493	576	506	618	427	517														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008NKF1L	10	207	766	630	713	590	656	545	592	496	727	608	693	582	621	723	525	609	537	648	459	550														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008PC1L	15	202	774	619	715	575	650	526	580	473	724	589	687	561	606	718	500	588	514	634	429	524														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008PKD1L	15	223	837	680	777	635	712	584	639	528	790	653	752	624	669	784	559	652	573	694	484	586														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008PKF1L	15	234	863	712	805	667	741	617	670	561	819	687	783	659	702	815	595	688	608	732	520	622														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008QK1L	20	216	829	662	765	[2]	696	[2]	[2]	[2]	775	[2]	735	[2]	648	768	[2]	[2]	[2]	[2]	[2]	[2]														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008QKD1L	20	239	897	729	833	680	763	626	685	566	847	700	806	668	717	841	599	699	614	749	519	628														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS008QKF1L	20	255	940	775	877	727	808	673	730	612	893	749	853	718	765	888	649	750	663	798	568	679														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010NK1L	20	224	866	687	798	636	723	581	642	521	809	653	765	621	672	801	551	651	567	704	472	578														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010NKD1L	20	243	921	742	852	690	777	634	695	571	867	711	823	678	729	860	606	710	621	763	521	635														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010NKF1L	20	255	949	776	882	725	810	669	729	607	899	749	857	716	765	894	644	749	659	800	561	675														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010PK1L	15	248	956	760	881	705	800	644	711	578	893	723	846	688	744	884	611	721	629	779	524	642														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010PKD1L	15	279	1051	851	974	793	891	730	799	659	991	817	942	779	837	984	698	816	716	875	603	732														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010PKF1L	15	293	1084	891	1010	834	929	771	838	701	1029	861	982	824	879	1023	743	861	760	918	649	778														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010QK1L	20	269	1035	824	954	765	867	699	772	628	967	785	916	747	807	958	664	782	683	845	569	696														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010QKD1L	20	304	1143	927	1061	865	971	795	871	718	1078	890	1026	850	912	1071	761	889	780	953	658	798														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010QKF1L	20	317	1171	964	1092	903	1005	835	907	759	1112	931	1062	892	951	1106	804	932	822	993	702	842														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010RK1L	25	286	1102	876	1015	813	922	743	820	667	1029	834	975	793	858	1019	705	831	726	898	[2]	740														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010RKD1L	25	325	1223	992	1135	924	1038	850	931	767	1153	951	1097	908	975	1145	813	950	834	1019	703	852														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010RKF1L	25	341	1260	1037	1175	971	1081	898	976	816	1196	1002	1142	959	1023	1190	866	1002	885	1068	756	906														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS010SK1L	30	360	1330	1095	1239	1026	1141	949	1031	864	1262	1058	1205	1013	1080	1256	915	1058	935	1127	800	958														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS016NK1L	10	285	1101	874	1014	809	920	740	817	664	1028	831	973	790	855	1018	702	828	722	896	[2]	737														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS016NKF1L	10	310	1174	946	1086	881	992	809	887	729	1105	907	1050	865	930	1097	773	906	793	893	667	811														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS016PK1L	10	328	1220	998	1135	933	1041	861	937	781	1156	963	1102	921	984	1150	829	964	848	1028	772	869														
MD	Inline Ultra Quiet Fan Splash Attenuation (K)	MDS016PKD1L	15	317	1222	972	1126	901	1023	824	909	739	1142	924	1081	879	951	1131	781	921	804	996																

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT		90		95		100		95		100		95		100		95		100					
					LWT	WB	80	85	80	85	80	85	80	85	80	85	80	85	80	85	80	85	80	85	80	85	80	85
							66	67	68	69	70	71	72	73	74	75	76	77	78	79	80	81	82	83	84	85	86	87
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5008ND1L	10	187.97	711	574	658	534	601	491	538	442	670	550	636	525	564	665	469	549	481	590	405	492				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5008NF1L	10	198.17	736	603	685	564	629	521	567	472	698	582	665	557	594	694	501	582	513	621	437	525				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5008PN1L	15	193.63	749	594	689	550	625	502	555	450	699	564	661	537	581	692	476	563	490	608	408	500				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5008PD1L	15	214.37	811	654	751	609	685	559	613	504	763	627	726	598	643	758	535	627	549	673	462	561				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5008PN1L	15	225.6	838	686	779	642	716	593	645	538	794	662	757	634	677	790	571	663	584	707	497	598				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010NC1L	10	206.37	803	633	738	585	667	534	591	477	748	601	707	571	619	741	506	599	521	649	432	531				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010ND1L	10	225.37	859	688	794	639	722	586	644	527	808	659	766	628	676	802	559	658	574	708	481	587				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010NF1L	10	237.13	888	722	824	673	754	620	677	561	840	696	800	665	711	835	597	696	610	744	518	626				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010PN1L	15	233.9	911	717	837	663	757	605	670	541	848	681	802	647	702	840	573	679	590	736	489	602				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010PD1L	15	263.93	1005	806	928	749	845	686	754	617	945	772	896	735	792	938	655	771	673	830	564	688				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010PN1L	15	278.07	1039	846	965	790	884	728	794	659	984	816	937	780	834	978	701	817	716	873	609	735				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010QC1L	20	252.77	982	775	902	717	817	654	724	585	915	736	865	700	758	906	620	734	638	795	529	651				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010QD1L	20	286.63	1087	875	1006	814	917	746	820	672	1023	838	972	799	860	1016	713	837	732	900	614	749				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010QF1L	20	299.9	1117	913	1038	853	952	786	857	713	1058	880	1008	842	900	1053	757	881	774	941	658	794				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010RC1L	25	270.97	1053	831	968	769	876	701	776	627	981	789	928	750	813	971	664	787	684	852	567	698				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010RD1L	25	309.7	1175	945	1087	879	991	806	886	726	1106	906	1050	863	929	1098	770	905	791	973	664	809				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5010RF1L	25	326.87	1217	995	1131	929	1038	857	934	777	1153	959	1099	918	981	1147	825	960	844	1025	718	865				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016NC1L	10	274.47	1073	842	984	778	889	709	785	121	998	799	942	759	823	988	671	797	691	864	[2]	705				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016ND1L	10	300.07	1150	917	1060	850	963	778	857	699	1079	877	1022	834	900	1071	742	876	763	944	[2]	780				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016NF1L	10	314.23	1183	957	1095	891	1000	820	896	740	1117	921	1062	880	943	1111	788	922	806	988	683	828				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016PN1L	15	306.33	1190	939	1094	869	990	793	877	710	1109	893	1049	848	919	1098	751	890	774	963	[2]	789				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016PD1L	15	338.47	1286	1033	1189	961	1084	881	968	793	1209	900	1148	943	1015	1201	842	989	864	1063	725	884				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016PF1L	15	355.47	1325	1082	1232	1010	1129	932	1015	844	1255	1043	1196	998	1066	1249	897	1044	917	1115	780	940				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016QC1L	20	331.67	1282	1017	1181	942	1071	860	951	771	1197	967	1133	919	995	1185	816	964	840	1042	698	856				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016QD1L	20	366.8	1386	1119	1284	1042	1173	957	1050	863	1306	1073	1241	1024	1100	1297	915	1072	939	1151	790	960				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016QF1L	20	384.07	1425	1168	1327	1093	1218	1009	1098	916	1352	1128	1289	1079	1152	1345	972	1129	994	1204	847	1019				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016RC1L	25	354.97	1373	1088	1264	1008	1146	921	1017	825	1281	1053	1212	984	1065	1269	873	1031	899	1116	747	916				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016RD1L	25	394.07	1489	1203	1379	1120	1260	1029	1128	927	1403	1135	1333	1100	1182	1393	984	1152	1009	1237	849	1032				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016RF1L	25	413.27	1533	1257	1427	1176	1311	1086	1182	986	1454	1214	1387	1161	1240	1446	1047	1215	1070	1295	912	1096				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016SN1L	30	376.6	1457	1155	1341	1069	1216	976	1079	875	1360	1098	1287	1043	1130	1346	926	1094	953	1184	792	972				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016SD1L	30	418.6	1682	1278	1466	1189	1338	1092	1198	984	1490	1225	1417	1168	1256	1480	1044	1224	1071	1314	901	1096				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5016SF1L	30	440.77	1534	1341	1522	1254	1398	1158	1266	1051	1550	1294	1479	1239	1322	1542	1116	1295	1141	1381	973	1169				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018NC1L	10	359.57	1395	1103	1283	1020	1162	932	1030	835	1301	1048	1230	996	1079	1288	883	1044	909	1131	[2]	927				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018ND1L	10	388.93	1480	1187	1368	1104	1246	1012	1112	911	1391	1137	1320	1084	1167	1381	967	1136	992	1222	833	1015				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018NF1L	10	405.17	1516	1233	1407	1151	1288	1060	1157	960	1434	1189	1366	1136	1215	1427	1020	1190	1046	1272	886	1070				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018PN1L	15	409.73	1589	1256	1462	1163	1324	1061	1174	951	1482	1194	1402	1135	1229	1467	1006	1190	1036	1288	861	1056				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018PD1L	15	446.97	1697	1365	1570	1269	1431	1164	1278	1048	1597	1307	1516	1246	1341	1585	1112	1306	1141	1404	958	1167				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018PN1L	15	466.27	1740	1419	1617	1325	1481	1222	1332	1107	1648	1368	1570	1308	1399	1639	1176	1370	1202	1463	1022	1233				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018QC1L	20	440.37	1804	1350	1568	1250	1422	1142	1262	1023	1590	1284	1505	1220	1321	1574	1083	1279	1115	1384	927	1137				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018QD1L	20	484.5	1734	1479	1698	1376	1550	1264	1386	1139	1727	1417	1641	1352	1454	1714	1208	1416	1239	1521	1042	1267				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018QF1L	20	508.83	1892	1548	1760	1447	1615	1336	1454	1211	1793	1494	1710	1429	1526	1784	1286	1495	1315	1595	1120	1348				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018RC1L	25	470.77	1823	1443	1677	1336	1520	1220	1349	1093	1700	1372	1609	1304	1412	1684	1157	1368	1191	1480	989	1215				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018RD1L	25	520.87	1972	1590	1826	1479	1666	1358	1449	1224	1857	1524	1764	1453	1563	1843	1298	1522	1332	1635	1120	1362				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018RF1L	25	544.33	2024	1656	1883	1548	1728	1429	1556	1296	1918	1598	1829	1529	1633	1908	1376	1599	1407	1707	1198	1442				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)	MD5018SN1L	30	496.07	2019	1521	1766	1408	1602	1286	1422	1152	1791	1446	1695	1374	1488	1773	1219	1441	1255	1559	1043	1280				
MD	Inline Quiet Fan w/ 2 ft Outlet Attenuators (N)																											

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT																			
					LWT		80		90		95		100		105		110		115		120			
					80	85	80	85	80	85	80	85	80	85	80	85	80	85	80	85	80	85		
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5008MQF1L	7.5	177.53	660	540	614	505	564	466	507	423	626	521	597	499	533	622	449	522	459	557	391	470
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5008NQCL	10	171.2	661	525	609	486	553	444	491	398	617	499	584	475	514	611	421	497	434	538	361	442
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5008NQDL	10	187.97	711	574	658	534	601	491	538	442	670	550	636	525	564	665	469	549	481	590	405	492
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5008NQFL	10	198.17	736	603	685	564	629	521	567	472	698	582	665	557	594	694	501	582	513	621	437	525
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5008PQCL	15	193.63	749	594	689	550	625	502	555	450	699	564	661	537	581	692	476	563	490	608	408	500
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5008PQDL	15	214.37	811	654	751	609	685	559	613	504	763	627	726	598	643	758	535	627	549	673	462	561
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5008PQFL	15	225.6	838	686	779	642	716	593	645	538	794	662	757	634	677	790	571	663	584	707	497	598
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010NQCL	10	206.37	803	633	738	585	667	534	591	477	748	601	707	571	619	741	506	599	521	649	432	531
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010NQDL	10	225.37	859	688	794	639	722	586	644	527	808	659	766	628	676	802	559	658	574	708	481	587
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010NQFL	10	237.13	888	722	824	673	754	620	677	561	840	696	800	665	711	835	597	696	610	744	518	626
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010PQCL	15	233.9	911	717	837	663	757	605	670	541	848	681	802	647	702	840	573	679	590	736	489	602
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010PQDL	15	263.93	1005	806	928	749	845	686	754	617	945	772	896	735	792	938	655	771	673	830	564	688
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010PQFL	15	278.07	1039	846	965	790	884	728	794	659	984	816	937	780	834	978	701	817	716	873	609	735
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010QQCL	20	252.77	982	775	902	717	817	654	724	585	915	736	865	700	758	906	620	734	638	795	529	651
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010QQDL	20	286.63	1087	875	1006	814	917	746	820	672	1023	838	972	799	860	1016	713	837	732	900	614	749
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010QQFL	20	299.9	1117	913	1038	853	952	786	857	713	1058	880	1008	842	900	1053	757	881	774	941	658	794
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010RQCL	25	270.97	1053	831	968	789	876	701	776	627	981	789	928	750	813	971	664	787	684	852	567	698
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010RQDL	25	309.97	1175	945	1087	879	971	806	886	726	1106	906	1050	863	929	1098	770	905	791	973	664	809
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5010RQFL	25	326.87	1217	985	1131	929	1038	857	934	777	1153	959	1099	918	981	1147	825	960	844	1025	718	865
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016NQCL	10	274.47	1073	842	984	778	889	709	785	621	938	799	942	759	823	988	671	797	691	864	621	705
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016NQDL	10	300.07	1150	917	1060	850	963	778	857	699	1079	877	1022	834	900	1071	742	876	763	944	621	780
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016NQFL	10	314.23	1183	957	1095	891	1000	820	896	740	1117	921	1062	880	943	1111	788	922	806	988	683	828
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016PQCL	15	306.33	1190	939	1094	869	990	793	877	710	1109	893	1049	848	919	1098	751	890	774	963	621	789
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016PQDL	15	338.47	1286	1033	1189	961	1084	881	968	793	1209	990	1148	942	1015	1201	842	989	864	1063	725	884
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016PQFL	15	355.47	1325	1082	1232	1010	1129	932	1015	844	1255	1043	1196	998	1066	1249	897	1044	917	1115	780	940
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016QQCL	20	331.67	1282	1017	1181	942	1071	860	951	771	1197	967	1133	919	995	1185	816	964	840	1042	698	856
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016QQDL	20	366.8	1386	1119	1284	1042	1173	957	1050	863	1306	1073	1241	1024	1100	1297	915	1072	939	1151	790	960
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016QQFL	20	384.07	1425	1168	1327	1093	1228	1098	1098	916	1352	1128	1289	1079	1152	1345	972	1129	994	1204	847	1019
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016RQCL	25	354.97	1373	1088	1264	1008	1146	921	1017	825	1281	1035	1212	984	1065	1269	873	1031	899	1116	747	916
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016RQDL	25	394.07	1489	1203	1379	1120	1260	1029	1128	927	1403	1153	1333	1100	1182	1393	984	1152	1009	1237	849	1032
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016RQFL	25	413.27	1533	1257	1427	1176	1311	1086	1182	986	1454	1214	1387	1161	1240	1446	1047	1215	1070	1295	912	1096
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016SQCL	30	376.6	1457	1155	1341	1069	1216	976	1079	875	1360	1098	1287	1043	1130	1346	926	1094	953	1184	792	977
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016SQDL	30	418.6	1682	1278	1466	1189	1338	1092	1198	984	1490	1225	1417	1168	1256	1480	1044	1224	1071	1314	901	1096
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5016SQFL	30	440.77	1634	1341	1522	1254	1398	1158	1260	1051	1550	1294	1479	1239	1322	1542	1116	1295	1141	1381	973	1169
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018NQCL	10	359.57	1395	1103	1283	1020	1162	932	1030	835	1301	1048	1230	996	1079	1288	883	1044	909	1131	821	927
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018NQDL	10	388.93	1480	1187	1368	1104	1246	1012	1112	911	1391	1137	1320	1084	1167	1381	967	1136	992	1222	833	1015
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018NQFL	10	405.17	1516	1233	1407	1151	1288	1060	1157	960	1434	1189	1366	1136	1215	1427	1020	1190	1044	1272	886	1070
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018PQCL	15	409.73	1589	1256	1462	1163	1324	1061	1174	951	1482	1194	1402	1135	1229	1467	1006	1190	1036	1288	861	1056
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018PQDL	15	446.97	1697	1365	1570	1269	1431	1164	1278	1048	1597	1307	1516	1246	1341	1585	1112	1306	1141	1404	958	1167
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018PQFL	15	466.27	1740	1419	1617	1325	1481	1222	1332	1107	1648	1368	1570	1308	1399	1639	1176	1370	1202	1463	1022	1233
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018QQCL	20	440.37	1704	1350	1568	1250	1422	1142	1262	1023	1590	1284	1505	1220	1321	1574	1083	1279	1110	1463	1022	1233
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018QQDL	20	484.5	1834	1479	1698	1376	1550	1264	1386	1139	1727	1417	1641	1352	1454	1714	1208	1416	1239	1521	1042	1267
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018QQFL	20	508.83	1892	1548	1760	1447	1615	1336	1454	1211	1793	1494	1710	1429	1526	1784	1286	1495	1315	1595	1120	1348
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018RQCL	25	470.77	1823	1443	1677	1336	1520	1220	1349	1099	1700	1372	1609	1304	1412	1684	1157	1368	1191	1480	989	1215
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018RQDL	25	520.87	1972	1590	1826	1479	1666	1358	1490	1224	1857	1524	1764	1453	1563	1843	1298	1522	1332	1635	1120	1362
MD	Inline Quiet Fan Splash Attenuation w/ 2 Ft Outlet Attenuators (Q)	MD5018RQFL	25	544.33	2024	1656	1883	1548	1728	1429	1556	1296	1											