

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown

[2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	HW CW WB	90	90	90	95	95	95	95	95	95	95	100	100	100	97	110	110	100	102	105	105	105
					80	80	80	80	80	80	80	85	85	85	85	85	85	85	85	85	87	85	85	80	90
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF702B082G-1	7.5		335	291	245	266	257	206	312	288	238	[2]	170	131	296	112	[2]	333	327	304	272	239	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF702B122G-1	7.5		386	347	294	318	284	249	370	343	285	[2]	205	157	352	133	[2]	384	387	361	325	286	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF702C082G-1	10		353	308	260	282	262	220	329	304	252	[2]	181	139	313	118	[2]	351	345	321	288	253	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF702C122G-1	10		419	367	311	336	301	264	392	363	302	[2]	218	169	372	142	[2]	417	410	382	344	303	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF702D082G-1	15		372	325	276	298	267	234	347	322	268	[2]	194	151	330	129	[2]	370	364	339	305	269	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF702D122G-1	15		448	394	335	361	325	285	419	389	326	[2]	237	184	399	158	[2]	445	438	409	370	327	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703C082G-1	10		455	397	336	362	324	283	426	394	328	[2]	236	184	406	157	[2]	457	449	417	375	330	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703C122G-1	10		531	466	395	426	381	333	499	463	386	[2]	278	217	476	186	[2]	533	524	488	440	388	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703C124G-1	10		421	365	306	331	295	257	393	362	299	[2]	1267	212	163	373	138	[2]	106	422	414	383	343
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703D082G-1	15		508	445	378	407	365	320	477	442	369	[2]	269	210	455	180	[2]	510	501	467	421	372	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703D122G-1	15		598	526	449	483	434	382	562	523	439	[2]	320	248	537	210	[2]	600	590	551	498	442	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703D124G-1	15		477	415	349	377	336	293	446	412	340	[2]	1411	243	188	424	160	[2]	123	478	469	435	390
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703E082G-1	20		545	476	403	434	389	342	510	473	394	[2]	287	227	486	196	[2]	547	537	499	449	396	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703E122G-1	20		643	566	483	519	467	411	605	562	472	[2]	346	272	578	231	[2]	645	634	592	536	475	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF703E124G-1	20		513	447	377	407	363	317	480	444	368	[2]	1502	264	204	457	174	[2]	134	515	505	469	421
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704D082G-1	15		684	605	519	542	488	432	656	612	513	[2]	1484	[1]	370	279	632	245	[2]	710	689	636	577
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704D122G-1	15		785	695	596	622	560	495	753	702	589	[2]	1484	[1]	421	312	725	270	[2]	814	790	729	663
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704D124G-1	15		696	604	507	549	488	425	655	604	498	[2]	2133	355	274	624	231	[2]	178	709	696	645	578
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704E082G-1	20		737	641	548	572	515	455	686	648	542	[2]	1484	[1]	389	297	670	285	[2]	755	732	674	611
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704E122G-1	20		835	741	637	665	601	533	801	748	630	[2]	1484	[1]	457	348	775	310	[2]	885	840	777	707
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704E124G-1	20		745	647	545	589	525	457	701	648	536	[2]	2254	383	297	669	251	[2]	193	759	745	691	620
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704G082G-1	25		756	670	576	601	543	483	725	677	570	[2]	1484	[1]	414	314	699	277	[2]	784	761	703	640
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704G122G-1	25		888	787	677	706	639	568	852	796	670	[2]	1484	[1]	490	381	822	342	[2]	921	895	826	752
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704G124G-1	25		788	687	580	626	559	488	743	687	570	[2]	2335	410	319	709	271	[2]	210	802	789	733	658
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704H082G-1	30		778	690	595	620	562	501	746	697	589	[2]	1484	[1]	432	330	720	292	[2]	806	783	724	659
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704H122G-1	30		922	818	705	734	665	592	885	826	697	[2]	510	391	853	347	[2]	956	928	858	781	700	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF704H124G-1	30		821	716	606	654	584	511	774	717	596	[2]	2403	430	336	739	285	[2]	221	835	821	763	686
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705F082G-1	22.5		1037	916	785	817	737	656	994	926	778	[2]	571	446	957	403	[2]	1076	1042	958	871	780	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705F122G-1	22.5		1162	1033	891	926	838	746	1116	1045	884	[2]	646	493	1078	444	[2]	1203	1167	1079	985	886	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705F124G-1	22.5		1074	940	799	859	771	677	1014	941	786	[2]	3028	574	450	969	386	[2]	301	1090	1071	998	901
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705H082G-1	30		1102	973	835	868	784	699	1055	984	827	[2]	610	482	1017	440	[2]	1143	1107	1018	926	830	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705H122G-1	30		1233	1098	956	986	896	801	1184	1110	942	[2]	699	542	1144	490	[2]	1276	1238	1145	1047	945	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705H124G-1	30		1139	1000	853	916	823	726	1076	1000	840	[2]	3180	[1]	619	489	1030	422	[2]	331	1155	1136	1060
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705J082G-1	40		1146	1018	880	913	829	742	1100	1029	872	[2]	651	517	1062	473	[2]	1186	1151	1062	970	875	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705J122G-1	40		1323	1181	1026	1064	969	870	1272	1193	1018	[2]	763	599	1230	546	[2]	1368	1328	1230	1128	1021	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705J124G-1	40		1210	1085	932	978	881	778	1145	1065	898	[2]	3180	[1]	686	529	1097	458	[2]	362	1227	1207	1128
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705K082G-1	45		1202	1068	926	961	874	785	1153	1080	919	[2]	690	549	1114	491	[2]	1245	1207	1115	1020	921	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705K122G-1	45		1359	1216	1060	1098	1002	901	1308	1229	1052	[2]	792	622	1266	565	[2]	1405	1365	1266	1163	1055	
MH Fluid Cooler	Standard Single Flow, Galvanized Coil	MHF705K124G-1	45		1260	1109	949	1018	917	811	1192	1110	935	[2]	3180	[1]	695	556	1142	486	[2]	391	1279	1258	1175
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706E082G-1	20		1330	1158	974	1048	934	814	1254	1158	957	[2]	679	516	1197	439	[2]	1357	1328	1228	1101	967	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706E122G-1	20		1550	1348	1133	1220	1085	941	1461	1349	1112	[2]	777	578	1394	487	[2]	1581	1547	1431	1282	1124	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706E124G-1	20		1367	1182	987	1067	946	819	1284	1182	968	[2]	3420	[1]	677	512	1222	429	[2]	321	1393	1365	1259
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706H082G-1	30		1474	1285	1084	1165	1040	908	1390	1286	1065	[2]	761	586	1328	505	[2]	1503	1472	1362	1223	1076	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706H122G-1	30		1737	1510	1267	1365	1214	1055	1637	1511	1244	[2]	880	685	1562	601	[2]	1772	1734	1603	1436	1258	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706H124G-1	30		1527	1323	1109	1196	1064	924	1436	1323	1087	[2]	3420	[1]	766	582	1367	490	[2]	369	1555	1524	1408
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706J082G-1	40		1587	1383	1169	1255	1122	983	1496	1384	1148	[2]	828	642	1429	554	[2]	1618	1584	1466	1317	1160	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706J122G-1	40		1874	1632	1376	1479	1320	1153	1766	1633	1352	[2]	965	745	1687	649	[2]	1911	1870	1731	1553	1366	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706J124G-1	40		1650	1443	1204	1297	1155	1005	1553	1433	1180	[2]	3420	[1]	834	637	1480	537	[2]	406	1680	1647	1523
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706L082G-1	50		1664	1439	1224	1314	1175	1029	1568	1450	1202	[2]	866	673	1497	581	[2]	1697	1661	1537	1379	1215	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706L122G-1	50		1963	1721	1461	1566	1402	1228	1856	1722	1435	[2]	1028	785	1776	679	[2]	2000	1960	1821	1641	1450	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706L124G-1	50		1725	1498	1259	1356	1208	1051	1623	1498	1235	[2]	3420	[1]	874	667	1547	562	[2]	425	1756	1722	1593
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706M082G-1	60		1736	1516	1283	1377	1232	1079	1638	1517	1261	[2]	908	708	1566	615	[2]	1769	1733	1606	1445	1274	
MH Fluid Cooler	Standard Double Flow, Galvanized Coil	MHF706M122G-1	60		2045	1789	1518	1627	1458	1279	1931	1791	1492	[2]	1076	836	1847	728	[2]	2083	2041	1894	1706	150	