

Capacity Represented in Water Flow (gpm)

[1] Water flow above maximum allowed for this model, maximum shown
 [2] Performance information not available for these conditions

Product	Model Group	Model	Fan BHP	Nominal Tons	EWT LWT WB	90	95	90	95	90	95	90	95	90	95	95	100	95	100	95	97	100	102	95	97	100	102
						80	85	80	85	80	85	80	85	80	85	85	85	85	85	85	85	85	85	85	85	85	85
Quadriflow (diamond or square layout)	Standard		21121	5	125	532	392	478	356	422	318	364	279	475	358	443	336	375	464	290	353	304	393	241	304		
Quadriflow (diamond or square layout)	Standard		21122	7.5	143	612	449	550	407	484	363	416	317	546	409	508	384	429	533	330	403	346	450	273	347		
Quadriflow (diamond or square layout)	Standard		21123	10	159	684	500	613	452	539	403	462	351	609	455	566	426	477	594	366	448	383	501	301	384		
Quadriflow (diamond or square layout)	Standard		21124	15	183	791	575	708	520	622	462	531	401	703	523	653	489	549	687	419	514	439	577	343	440		
Quadriflow (diamond or square layout)	Standard		21221	10	186	792	584	712	530	628	474	541	414	707	533	659	500	558	691	431	525	451	585	357	452		
Quadriflow (diamond or square layout)	Standard		21222	15	211	904	663	811	600	714	536	613	467	806	604	749	566	633	787	487	594	510	665	402	511		
Quadriflow (diamond or square layout)	Standard		21321	10	204	863	639	777	582	687	521	594	458	772	585	720	550	612	755	476	576	498	641	396	499		
Quadriflow (diamond or square layout)	Standard		21322	15	232	986	728	887	661	783	591	675	518	881	665	821	624	696	861	539	654	564	730	447	565		
Quadriflow (diamond or square layout)	Standard		21323	20	256	1091	803	981	729	855	651	744	569	974	733	907	688	768	952	593	722	621	806	490	622		
Quadriflow (diamond or square layout)	Standard		22121	10	243	1034	763	930	692	821	618	706	540	924	696	861	653	729	903	563	685	589	765	465	590		
Quadriflow (diamond or square layout)	Standard		22122	15	276	1177	867	1059	786	934	700	802	610	1052	790	979	740	828	1028	636	777	667	869	524	668		
Quadriflow (diamond or square layout)	Standard		22123	20	304	1300	955	1168	865	1030	770	883	670	1161	870	1080	815	912	1134	699	856	733	958	574	734		
Quadriflow (diamond or square layout)	Standard		22221	15	312	1322	979	1191	889	1053	795	907	695	1183	894	1103	839	936	1156	724	880	758	982	599	759		
Quadriflow (diamond or square layout)	Standard		22222	20	342	1452	1073	1308	974	1155	870	994	759	1299	980	1211	919	1026	1270	791	964	828	1077	653	830		
Quadriflow (diamond or square layout)	Standard		22223	25	368	1564	1155	1408	1048	1244	935	1070	815	1399	1054	1304	988	1104	1368	849	1037	890	1159	700	892		
Quadriflow (diamond or square layout)	Standard		22224	30	389	1655	1221	1490	1107	1316	987	1131	860	1480	1114	1379	1044	1167	1447	896	1096	940	1225	738	942		
Quadriflow (diamond or square layout)	Standard		22225	40	425	1803	1334	1626	1210	1437	1078	1235	938	1616	1217	1506	1140	1275	1579	978	1197	1026	1339	804	1028		
Quadriflow (diamond or square layout)	Standard		23121	20	390	1593	1212	1448	1109	1295	1000	1130	881	1448	1122	1359	1059	1170	1421	923	1109	962	1225	772	968		
Quadriflow (diamond or square layout)	Standard		23122	25	416.5	1701	1294	1548	1185	1383	1067	1207	941	1546	1199	1451	1131	1249	1518	985	1185	1028	1308	825	1034		
Quadriflow (diamond or square layout)	Standard		23123	30	437.3	1787	1359	1626	1244	1453	1120	1267	987	1624	1259	1524	1187	1312	1594	1034	1244	1079	1374	865	1086		
Quadriflow (diamond or square layout)	Standard		23124	40	475	1862.9 [1]	1476	1662.9 [1]	1351	1578	1218	1376	1074	1662.9 [1]	1367	1655	1290	1425	1662.9 [1]	1125	1351	1173	1492	941	1180		
Quadriflow (diamond or square layout)	Standard		23221	20	419.3	1703	1304	1552	1195	1390	1079	1216	954	1549	1208	1456	1141	1258	1521	998	1194	1040	1316	840	1046		
Quadriflow (diamond or square layout)	Standard		23222	25	447.7	1819	1392	1657	1276	1484	1152	1298	1019	1654	1289	1554	1218	1343	1624	1066	1275	1111	1405	897	1117		
Quadriflow (diamond or square layout)	Standard		23223	30	469.5	1910	1460	1739	1338	1557	1208	1361	1067	1736	1352	1631	1277	1408	1705	1117	1337	1164	1474	939	1171		
Quadriflow (diamond or square layout)	Standard		23224	40	511.5	1922.9 [1]	1591	1893	1459	1695	1317	1483	1165	1889	1474	1775	1392	1535	1855	1219	1457	1270	1606	1027	1277		
Quadriflow (diamond or square layout)	Standard		23225	50	548.3	1922.9 [1]	1705	1922.9 [1]	1563	1817	1412	1590	1248	1922.9 [1]	1579	1903	1492	1645	1922.9 [1]	1306	1562	1361	1721	1100	1369		
Quadriflow (diamond or square layout)	Standard		24121	15	531.4	2157	1646	1962	1511	1756	1368	1537	1215	1966	1532	1846	1449	1594	1932	1271	1517	1322	1669	1078	1332		
Quadriflow (diamond or square layout)	Standard		24122	20	587.8	2386	1821	2171	1672	1943	1513	1701	1344	2175	1695	2042	1602	1763	2138	1407	1678	1463	1847	1193	1474		
Quadriflow (diamond or square layout)	Standard		24123	25	634.2	2576	1965	2343	1803	2096	1632	1835	1449	2347	1829	2204	1729	1903	2307	1517	1810	1578	1993	1286	1589		
Quadriflow (diamond or square layout)	Standard		24124	30	673.8	2736	2087	2489	1916	2227	1734	1949	1540	2493	1943	2341	1837	2021	2451	1612	1923	1676	2117	1367	1689		
Quadriflow (diamond or square layout)	Standard		24125	40	738.9	3001	2289	2729	2101	2442	1901	2137	1688	2734	2130	2568	2014	2217	2688	1767	2109	1838	2321	1498	1851		
Quadriflow (diamond or square layout)	Standard		24126	50	793.4	3222	2458	2931	2256	2623	2042	2295	1813	2936	2287	2757	2162	2380	2886	1898	2264	1973	2493	1609	1988		
Quadriflow (diamond or square layout)	Standard		24127	60	836.7	3393	2592	3088	2380	2764	2155	2421	1915	3093	2413	2905	2282	2510	3041	2004	2389	2083	2628	1700	2099		
Quadriflow (diamond or square layout)	Standard		24221	25	796.5	3225	2467	2937	2265	2631	2051	2305	1820	2942	2297	2765	2172	2390	2893	1906	2274	1982	2502	1614	1997		
Quadriflow (diamond or square layout)	Standard		24222	30	843.6	3417	2613	3111	2399	2787	2171	2441	1927	3117	2432	2929	2300	2531	3064	2018	2408	2098	2650	1709	2114		
Quadriflow (diamond or square layout)	Standard		24223	40	922.7	3738	2858	3403	2624	3048	2375	2669	2108	3409	2660	3203	2515	2768	3352	2207	2634	2295	2898	1869	2312		
Quadriflow (diamond or square layout)	Standard		24224	50	989	4006	3063	3648	2812	3268	2545	2861	2259	3654	2852	3434	2696	2967	3593	2365	2823	2460	3107	2003	2478		
Quadriflow (diamond or square layout)	Standard		24225	60	1047	4241	3243	3862	2977	3459	2694	3029	2391	3869	3019	3635	2854	3141	3804	2504	2988	2604	3289	2120	2623		